

# MENB1030

Universal 30 Watt Series

Medical Switch-Mode Power Supply



3 Year Warranty

- 100-240VAC Universal Input
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- Certified to UL/EN60601—1, **3<sup>rd</sup> Edition**
- 5V to 48V outputs, up to 32W
- Modified and Custom Designs Available
- Regulated Output with Low Ripple
- Impact-Resistant Polycarbonate Enclosure
- No load Power Consumption <0.3W
- Desktop & Wall Plug Styles



## Specifications

All Specifications are typical at nominal input, full load at 25°C unless otherwise stated.

|                                |                                                                                       |                          |                                                                                                                 |
|--------------------------------|---------------------------------------------------------------------------------------|--------------------------|-----------------------------------------------------------------------------------------------------------------|
| AC Input                       | 100-240VAC, +/-10%, 47-63 Hz, 1Ø                                                      | MTBF                     | >100,000 hours calculated                                                                                       |
| Input Current                  | 100VAC: 0.9A                                                                          | Hold-up Time             | 18 ms min. @ 115VAC, 60 msec @ 230VAC                                                                           |
| Inrush Current                 | 60A peak, 264Vac, cold start                                                          | Turn-on Time             | 2 seconds, max.                                                                                                 |
| Input Fuse                     | 3.15A Internal Primary Current Fuse is provided                                       | Topology                 | Switching – Fixed Frequency Flyback                                                                             |
| Efficiency                     | Meets EISA2007, CEC Efficiency Level V, and EU(EC) No. 278/2009 Phase II requirements | Overload Protection      | Hiccup Mode                                                                                                     |
| Output Voltage                 | See chart                                                                             | Short Circuit Protection | Hiccup Mode                                                                                                     |
| Output Power                   | See chart                                                                             | EMC                      | See chart below                                                                                                 |
| Ripple and Noise               | 1% pk-pk max., 20MHz BW                                                               | Safety Standards         | EN/IEC/CSA/UL60601-1, 3rd Edition                                                                               |
| Line & Load Voltage Regulation | Line: +/- 1%, Load: +/-5%                                                             | Dielectric Withstand     | Input-Output: 5,656VDC, Input-GND: 1,500 Vac, Output-GND: 500Vdc                                                |
| Transient Response             | 500µs max., 50% load step, typical                                                    | Operating Temperature    | 0° to 40°C, no derating                                                                                         |
| Minimum Load                   | Not required                                                                          | Storage Temperature      | -30 to +85°C                                                                                                    |
| Case Material:                 | Black 94V0 Polycarbonate                                                              | Relative Humidity        | 5% to 95%, non-condensing                                                                                       |
| Case Dimensions:               | 95 x 54 x 31mm. See outline drawing<br>Weight = 200g                                  | Altitude                 | 0 to 10,000 ft                                                                                                  |
| Output Connector:              | 2.5mm barrel type (Ault #3) connector, center contact (+). Other options available    | Output Cable:            | 5V – 9V models: #18AWG (SPT-1), 1,500mm, 2 conductor<br>12V – 24V models: #18AWG (UL1185), 1,500mm, 2 conductor |

## EMC Specifications

|                                         |                                                       |
|-----------------------------------------|-------------------------------------------------------|
| Conducted Emissions                     | EN55011 Class B, FCC Part 15, Class B.                |
| Radiated Emissions                      | EN55011 Class B, FCC Part 15, Class B.                |
| Line Frequency Harmonics                | EN61000-3-2, Class A                                  |
| Voltage Fluctuations/Flicker            | EN61000-3-3                                           |
| Static Discharge Immunity               | EN61000-4-2, 6kV Contact Discharge, 8kV air discharge |
| Radiated RF Immunity                    | EN61000-4-3, 3V/m.                                    |
| EFT/Burst Immunity                      | EN61000-4-4, 2kV/5kHz.                                |
| Line Surge Immunity                     | EN61000-4-5, 1kV differential, 2kV common-mode        |
| Conducted RF Immunity                   | EN61000-4-6, 3Vrms                                    |
| Power Frequency Magnetic Field Immunity | EN61000-4-8, 3A/m                                     |
| Voltage Dip Immunity                    | EN61000-4-11, Criteria A                              |

# MENB1030

Universal 30 Watt Series



Medical Switch-Mode Power Supply

3 Year Warranty

| Model Number     | Volts (V) | Output Current (max) | Max Watts | Ripple (Vp-p max) |
|------------------|-----------|----------------------|-----------|-------------------|
| MENB1030A0503F01 | 5 V       | 4.00 A               | 20.0 W    | 50 mV             |
| MENB1030A0703F01 | 7.5 V     | 3.00 A               | 22.5 W    | 75 mV             |
| MENB1030A0903F01 | 9 V       | 3.00 A               | 27.0 W    | 90 mV             |
| MENB1030A1203F01 | 12 V      | 2.50 A               | 30.0 W    | 120 mV            |
| MENB1030A1403F01 | 14 V      | 2.10 A               | 29.4 W    | 140 mV            |
| MENB1030A1503F01 | 15 V      | 2.00 A               | 30.0 W    | 150 mV            |
| MENB1030A1803F01 | 18 V      | 1.67 A               | 30.0 W    | 180 mV            |
| MENB1030A2403F01 | 24 V      | 1.33 A               | 31.9 W    | 240 mV            |
| MENB1030A4803F01 | 48 V      | 0.63 A               | 30.0 W    | 480 mV            |

Notes: Part numbers above include #3 output connector and IEC320 C14 grounded input receptacle. See below for other options.

## Model Number Key

**MENB 1 030 A VV 03 F 01**

|                          |                                                                               |
|--------------------------|-------------------------------------------------------------------------------|
| <b>Model</b>             | "01" = Standard. "02" and higher indicates a modified model.                  |
| <b>Input Connector:</b>  | "F" = IEC320 C14 grounded, Other options available, see below                 |
| <b>Output Connector:</b> | "03" = 2.5mm Barrel Type Connector. Other options available, contact factory. |
| <b>Output Voltage:</b>   | "05" = 5Vdc, "12" = 12Vdc, "24" = 24Vdc, etc.                                 |
| <b>Model</b>             | "A" = Original Configuration                                                  |
| <b>Output Power:</b>     | "030" = 30 Watts                                                              |
| <b># of Outputs</b>      | "1" = Single Output                                                           |
| <b>Product Family:</b>   | "M" = Medical, "E" = External, "NB" = Model Series Designator                 |


## AC Input Receptacle Options

| Desktop                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |                                               |                                            | Wall-Plug                                     |                                     |                        |                                   |                           |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------|--------------------------------------------|-----------------------------------------------|-------------------------------------|------------------------|-----------------------------------|---------------------------|
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |                                               |                                            |                                               |                                     |                        |                                   |                           |
| IEC320 - C14<br>Class I<br>Grounded<br>(F)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | IEC320 - C18<br>Class II<br>Ungrounded<br>(Q) | IEC320 - C8<br>Class II<br>"Shaver"<br>(N) | N. America<br>Japan<br>Interchangeable<br>(C) | N. America<br>Japan<br>Fixed<br>(B) | Europe<br>Fixed<br>(M) | United<br>Kingdom<br>Fixed<br>(G) | Australia<br>Fixed<br>(H) |
| Notes: 1. For desktop options, choose applicable letter above.<br>2. For Wall-Plug options, choose the applicable letter above and the unit will be fitted with the receptacle chosen. The N. A. blade version (C) will be an interchangeable blade. The other options (B), (M), (G), and (H) will be fixed blades molded in the case.<br>3. Blade Kit is available which will include one each of a EU, UK, and Australian blade. Kit part # is KT1027K. These can be used with the (C) version, to allow blades to be changed. |                                               |                                            |                                               |                                     |                        |                                   |                           |

## Output Connector

|  |                                                                                                                                                                                                                                                                  |
|--|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | Notes: 1. Ault #3 Connector, center contact (+).<br>2. Connector is Switchcraft 760 plug or equivalent. Mating connector is Switchcraft 712A or equivalent.<br>3. Other connector options are available. Contact your local SL Power Representative for details. |
|--|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## Outline Drawings



Desktop Style

Wall-plug Style ("B" Option Shown)

Data Sheet © 2011 SL Power Electronics Corp. The information and specifications contained herein are believed to be correct at the time of publication. Rev. 9-12-2011  
 However, SL Power accepts no responsibility for consequences arising from reproduction errors or inaccuracies. Specifications are subject to change without notice.