

Pin Definition:

1. Base
2. Collector
3. Emitter

PRODUCT SUMMARY

BV_{CBO}	1050V
BV_{CEO}	550V
I_C	5A
V_{CE(SAT)}	0.5V @ I _C =1A, I _B =200mA

Features

- High Voltage Capability
- High switching speed

Ordering Information

Part No.	Package	Packing
TSC1203ECM RNG	TO-263	800pcs / 13" Reel

Note: "G" denote for Halogen Free Product

Absolute Maximum Rating (T_A=25°C unless otherwise noted)

Parameter	Symbol	Limit	Unit
Collector-Base Voltage	V _{CBO}	1050	V
Collector-Emitter Voltage	V _{CEO}	550	V
Emitter-Base Voltage	V _{EBO}	9	V
Collector Current	DC	5	A
	Pulse(T _p <5ms)	8	
Base Current	DC	2	A
	Pulse(T _p <5ms)	4	
Collector Power Dissipation	T _C =25°C	36	W
Operating Junction Temperature	T _J	+150	°C
Operating Junction and Storage Temperature Range	T _{STG}	- 55 to +150	°C

Electrical Specifications (T_A=25°C unless otherwise noted)

Parameter	Conditions	Symbol	Min	Typ	Max	Unit
Collector-Base Breakdown Voltage	I _C =1mA, I _B =0	BV _{CBO}	1050	--	--	V
Collector-Emitter Breakdown Voltage	I _C = 5mA, I _E =0	BV _{CEO}	550	--	--	V
Emitter-Base Breakdown Voltage	I _E =10mA, I _C =0	BV _{EBO}	9	--	--	V
Collector Cutoff Current	V _{CE} =1050V, V _{BE} =0	I _{CES}	--	--	100	uA
Collector Cutoff Current	V _{CE} =550V, I _B =0	I _{CEO}	--	--	100	uA
Emitter Cutoff Current	V _{EB} =9V, I _C =0	I _{EBO}	--	--	10	uA
Collector-Emitter Saturation Voltage	I _C =1A, I _B =200mA	V _{CE(SAT)1}	--	0.12	0.5	V
	I _C =2A, I _B =400mA	V _{CE(SAT)2}	--	0.18	0.7	
	I _C =3A, I _B =1A	V _{CE(SAT)3}	--	0.22	1.5	
Base-Emitter Saturation Voltage	I _C =2A, I _B =400mA	V _{BE(SAT)1}	--	0.87	1.5	V
	I _C =3A, I _B =1A	V _{BE(SAT)2}	--	0.95	1.5	
DC Current Transfer Ratio	V _{CE} =5V, I _C =1mA	h _{FE} 1	10	--	--	
	V _{CE} =5V, I _C =10mA	h _{FE} 2	10	--	--	
	V _{CE} =5V, I _C =2A	h _{FE} 3	9	--	28	
	V _{CE} =3V, I _C =800mA	h _{FE} 4	14	--	32	

Resistive Load Switching Time (Ratings)

Turn-on Time	V _{CC} = 150V, I _C = 2A,	t _{on}	--	--	0.5	uS
Storage Time	I _{B1} = 0.4A, I _{B2} = -0.8A,	t _s	--	2.5	3.5	uS
Fall Time	t _p = 30uS	t _f	--	0.2	0.3	uS

Electrical Characteristics Curve ($T_A=25^\circ\text{C}$, unless otherwise noted)

Figure 1. Static Characteristics




Figure 2. DC Current Gain




Figure 3. $V_{CE(SAT)}$ vs. Collector Current




Figure 4. $V_{BE(SAT)}$ vs. Collector Current




Figure 5. Safety Operating Area






Figure 6. Reverse Bias SOA




TO-263 Mechanical Drawing



Unit: Millimeters

Land Pattern Recommendation



Marking Diagram



Y = Year Code

M = Month Code for Halogen Free Product

O =Jan **P** =Feb **Q** =Mar **R** =Apr

S =May **T** =Jun **U** =Jul **V** =Aug

W =Sep **X** =Oct **Y** =Nov **Z** =Dec

L = Lot Code (1~9, A~Z)

Not Recommended

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.