

Chip Beads

Product Top Page

Search by Part No.

Search by Characteristics

Cross Reference

Catalog

Tech Note

Technical Support Tool

FAQ

MMZ1608R301CTAH0

?

RoHS

REACH SVHC Free

Halogen Free

Lead Free

Applications

Commercial Grade

Feature

Signal

Signal line


Series

MMZ

Status

Production (Not Recommended for New Design)

Recommended Alternate Part No. : [MMZ1608R301ATA00](#)



Images are for reference only and show exemplary products.

PDF file of this page

Contact

- Documents
- Product Lineup
 - Sample Kits



- Technical Support Tools
- S-parameter
 - SPICE Netlist (Simple)
 - Equivalent Circuit Model

Size	
Length(L)	1.60mm ±0.15mm
Width(W)	0.80mm ±0.15mm
Thickness(T)	0.60mm ±0.15mm
Recommended Land Pattern (A)	0.60mm Nom.
Recommended Land Pattern (B)	0.80mm Nom.
Recommended Land Pattern (C)	0.80mm Nom.

Electrical Characteristics	
Impedance at 100MHz	300Ω ±25%
Rated Current	500mA
DC Resistance (Max.)	250mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125°C
Soldering Method	Reflow Iron Soldering
AEC-Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000pcs
Weight	0.003g

Characteristic Graph (This is reference data, and does not guarantee the products characteristics.)



Products

» Search by Part No.

» Search by Characteristics

» Distributor Inventory Check

» Capacitors

» Inductors (Coils)

» EMC Components

» RF / SAW Components and Modules

» Voltage / Current / Temperature Protection Devices

» Sensors and Sensor Systems

» Ceramic Switching / Heating, Piezo Components and Buzzers

» Transformers

» Ferrites and Accessories

» Noise Suppressing / Magnet Sheets

» Anechoic Chambers and Radio Wave Absorbers

» Power Supplies

» Magnets

» Flash Storages

» Wireless Charging

» FA Systems

» Transparent Conductive Film

» Micro Modules (Substrates with Built-in ICs, Products Utilizing with SESUB)

» Solar Cells

Application Guides

Technical Support

Tech Library

Environment

Contact

News

Home

About TDK

TDK Worldwide