



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	POWER										SIGNAL							
		E1	P1	P2	P3	P4	P5	P6	P7	P8	P9	P10	1	2	3	4	5	6	E2
51732-050-- NOTE 3	D C B A		PA	PA	PA	PA	PA	PA	PA	PA	PA	PA	UUUUUU	TTTTTT	SSSSSS	LLLLLL			



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
U	[6.86]	SIGNAL
T	[6.86]	SIGNAL
S	[6.86]	SIGNAL
R	[6.86]	SIGNAL
PA	[N/A]	POWER
E	[5.59]	SIGNAL

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date	linear		0.X ±0.5		COPY		www.fciconnect.com	
A	DG09-0082	WD	03/20/09			0.XX ±0.25		projection		title 10P + 24S RIGHT ANGLE SOLDER HEADER	
				angles		0.XXX ±0.1				product family PwrBlade code 213	
				dr	Warren Du	02/10/09		MIM		size dwg no 51732-050 sheet 1 of 4	
				enrg	Warren Du	02/10/09		scale			
				chr	PM ZHENG	02/10/09		1:1			
				appd	JOSEPH HSIA	02/10/09					
sheet index	revision sheet	A	A	A	A					cage code 22526	
		1	2	3	4						

Pro/E





cage code 22526

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51732-050--
NOTE: 3



mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date	linear		0.X ±0.5		COPY		www.fciconnect.com	
A						0.XX ±0.25		projection		title 10P + 24S	
						0.XXX ±0.1				RIGHT ANGLE SOLDER HEADER	
					angles	0° ±2°					
				dr	Warren Du	02/10/09		MIM		product family	PwrBlade
				enr	Warren Du	02/10/09				size	213
				chr	PM ZHENG	02/10/09				dwg no	2 of 4
				appd	JOSEPH HSIA	02/10/09				51732-050	
sheet index	revision sheet							scale	1:1		

Pro/E


cage code 22526

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51732-050--
NOTE: 3



RECOMMENDED PCB LAYOUT

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date					COPY		www.fciconnect.com	
A				linear		0.X ± 0.5		projection		title 10P + 24S	
						0.XX ± 0.25				RIGHT ANGLE SOLDER HEADER	
				angles		0.XXX ± 0.1				product family PwrBlade	
						0° ± 2°				code 213	
				dr	Warren Du	02/10/09		MIM		size	
				enrg	Warren Du	02/10/09				dwg no 51732-050	
				chr	PM ZHENG	02/10/09		scale		sheet 3 of 4	
				appd	JOSEPH HSIA	02/10/09		1:1			
sheet index	revision sheet										

Pro/E

cage code 22526

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

B

B