



Part Number : [500348000](#)
Product Description : 2.00mm Pitch, Board-in
Crimp Terminal, Male, Vertical, Phosphor Bronze Tin
Plated, 30-26 AWG, Reel
Series Number : 50034
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

[500348000 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[500349200-SPK-200.pdf](#)

[510151002-PS-000.pdf](#)

Tooling Specifications

[CS-50034-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	50034
Description	2.00mm Pitch, Board-in Crimp Terminal, Male, Vertical, Phosphor Bronze Tin Plated, 30-26 AWG, Reel
Application	Signal, Wire-to-Board
Comments	Right-angle, Use with housing 35023
Product Name	Board-in
UPC	800753576261

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	125V AC (RMS)/DC

Physical

Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin

Material - Plating Termination	Tin
Net Weight	0.050/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.40mm max.
Wire Size (AWG)	26, 28, 30
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
2.00mm Pitch Board-In Vertical Crimp Housings	<u>51015</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for 2.00mm Pitch Board-in Crimp Terminals	<u>638234900</u>
FineAdjust Applicator for 2.00mm Pitch Wire-to-Wire Terminal, 30-26 AWG Wire	<u>639004000</u>

Japan

Description	Part Number
S-1 Applicator for Board-in Terminal, 30-26 AWG, for Twisted Wire Only	<u>570553700</u>