


THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO POSITRONIC AND IT'S SUBSIDIARIES. POSITRONIC BELIEVES THE DATA ON THIS DRAWING TO BE RELIABLE, SINCE THE TECHNICAL INFORMATION IS GIVEN FREE OF CHARGE, THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.


SK5160

DATE	REV	REVISION RECORD	APP	DR	CK
3-30-10	B	ECO 32310	TK	BS	TK
10-18-11	C	ECO 34603	COLE	BS	COLE
10-31-11	D	ECO 34658	COLE	ME	COLE
11-10-11	E	ECO 34729	COLE	BS	COLE









PANEL CUT OUT

NOTES:
1. MATERIALS AND FINISHES:
   INSULATOR: GLASS FILLED POLYESTER, UL 94V-0, COLOR: BLUE.
   CONTACTS: PRECISION MACHINED COPPER ALLOY, GOLD FLASH OVER NICKEL PLATE.
2. DETAILED PRODUCT, MECHANICAL, AND ELECTRICAL INFORMATION IS AVAILABLE IN THE LATEST COMPACT POWER CONNECTOR PRODUCT PUBLICATION. VISIT CONNECTPOSITRONIC.COM/PRODUCTS/33/COMPACTPOWERCONNECTORS OR CONNECTPOSITRONIC.COM.
3. CONTACTS CALLED OUT FOR REFERENCE ONLY, CONTACTS ORDER SEPARATELY. USE FC422N8 CONTACTS FOR SIZE 22 CONTACTS, SEE TABLE FOR SIZE 16 CONTACTS.
4. DIMENSIONS ARE IN MILLIMETERS [INCHES].

PART NUMBER	WIRE SIZE mm² /[awg]
FC112N2S-1565.0	4.0/[12]
FC114N2-1565.0	2.5-1.5/[14-16]
FC116N2-1565.0	1.5-1.0/[16-18]

POSITRONIC INDUSTRIES INC.
www.connectpositronic.com
FSCM 28198

DECIMAL TOL. ±0.38 [0.015]
ANGULAR TOL. ±5°

PCIB SERIES | SCALE N.T.S. | DRAWN BY M. ENEA | APPROVED BY RCW

TITLE: PCIB24W9F8000

DATE: 10-1-03 | DRAWING NUMBER: SK5160 | REV.: E

Downloaded from Arrow.com.