



Part Number : [1707290005](#)

Product Description : iPass+ zHD Vertical Single Piece Housing Assembly, Through Hole, 0.76µm Gold (Au) Plating

Series Number : 170729

Status : Active

Product Category : High-Speed I/O Connectors



Documents and Resources

Drawings

[1707290005_sd.pdf](#)

[PK-76867-002-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[EE-170729-0001-001.pdf](#)

[SP-170729-0001-001.zip](#)

Specifications

[1707290002-000.pdf](#)

[AS-170729-0001-001.pdf](#)


[PS-170729-001-001.pdf](#)

[1707290001-000.pdf](#)

[TS-170729-9906-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	High-Speed I/O Connectors
Series	170729
Description	iPass+ zHD Vertical Single Piece Housing Assembly, Through Hole, 0.76µm Gold (Au) Plating
Application	Wire-to-Board
Component Type	Internal Receptacle
Product Name	iPass+,zHD
Type	Pluggable
UPC	887191414942

Agency

CSA	LR19980
UL	E107635

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	48V AC (RMS) / 67V DC

Physical

Circuits (Loaded)	36
Circuits (maximum)	36
Color - Resin	Black
Durability (mating cycles max)	50
Flammability	94V-0
Gender	Receptacle
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.798/g
Number of Rows	4
Orientation	Vertical
Packaging Type	Tray
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
PC Tail Length	1.37mm
Pitch - Mating Interface	0.75mm
Plating min - Mating	0.760µm
Plating min - Termination	0.760µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-40° to +80°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Internal iPass+ HD-to-iPass+ HD, 4X Short Body Cable Assemblies	<u>100171</u>
Internal iPass+ HD-to-iPass+ HD, 8X Short Body Cable Assemblies	<u>100172</u>
Internal iPass+ HD-to-iPass+ HD, 4X Short Body Cable Assemblies	<u>100189</u>
Internal iPass+ HD-to-iPass+ HD, 8X Short Body Cable Assemblies	<u>100190</u>
Internal iPass+ HD-to-iPass+ HD, 4X Short Body Cable Assemblies	<u>100219</u>
Internal iPass+ HD-to-iPass+ HD, 8X Short Body Cable Assemblies	<u>100220</u>
Internal iPass+ HD-to-iPass+ HD, 4X Short Body Cable Assemblies	<u>100221</u>
Internal iPass+ HD-to-iPass+ HD, 4X Short Body Cable Assemblies	<u>100222</u>
Internal iPass+ HD-to-iPass+ HD, 4X Short Body Cable Assemblies	<u>100223</u>
Internal iPass+ HD-to-iPass+ HD, 8X Short Body Cable Assemblies	<u>100224</u>
Internal iPass+ HD-to-iPass+ HD, 8X Short Body Cable Assemblies	<u>100225</u>
Internal iPass+ HD-to-iPass+ HD, 8X Short Body Cable Assemblies	<u>100226</u>

Application Tooling

Global

Description	Part Number
iPass+ zHD Vertical Housing Assembly Removal Tool	<u>622024800</u>
iPass+ zHD Wafer Assembly Removal Tool	<u>622024900</u>

This document was generated on May 06, 2026