

CKG57KX7S1H106M335JH

TDK item description : CKG57KX7S1H106MT***




Application & Main Feature

Commercial grade (MEGACAP)

Series

CKG57K(5750) [EIA 2220]



Dimensions

L 6.00±0.50 mm
W 5.00±0.50 mm
T 3.35±0.15 mm
E 1.60±0.30 mm

Temperature Characteristic

X7S (-55 to +125 degC, ±22%)

Rated Voltage

1H (50Vdc)

Capacitance

10µF

Capacitance Tolerance

M (±20%)

DF






5 % max.

Insulation Resistance

50 Mohm min.

AEC-Q200

Not Applicable



Characterization Sheet (Multilayer Ceramic Chip Capacitors)



⚠ All specifications are subject to change without notice.

April 8, 2022