

REVISIONS			
REV	ECN, ERN NO.	DATE	APPRD.
F	PRODUCT DRAWING (EAR 14498)	NOV9/16	K.L.



CAPACITANCE SCHEMATIC
FOR EACH POSITION



ORDERING CODE: F C E 1 7 – E 0 9 S C – 3 5 0 G

SERIES
FCE17=FILTERED D–SUB, RoHS

SIZE/NUMBER OF CONTACTS
E09, A15, B25, OR C37

CONNECTOR STYLE
P=PIN
S=SOCKET

TERMINATION TYPE
C=.590"[14.99] FOOTPRINT

MOUNTING
2=.120 [3.05] DIA THROUGH HOLE
3=#4–40 UNC SELF–LOCKING THREAD
4=#4–40 UNC THREAD
6=M3 x 0.5 THREAD
E=CODE 4 MOUNTING WITH #4–40 UNC
HEX JACK SOCKET SUPPLIED.
F=#4–40 UNC THREAD IN
ø.187 [ø4.75] FIXED JACK SOCKET

CONTACT FINISH/GOLD THICKNESS
NO DIGIT=STANDARD 15 MICROINCHES
[0.38 MICRONS] GOLD ON
MATING AREA
G=50 MICROINCHES [1.27 MICRONS]
GOLD ON MATING AREA


MODIFIER
0=STANDARD


FILTER CAPACITANCE

D=50 pF	5=1000 pF
B=100 pF	7=1200 pF
0=180 pF	6=1300 pF
F=330 pF	J=1500 pF
L=380 pF	E=2200 pF
1=470 pF	9=5600 pF
4=820 pF	8=47000 pF
	N=NO FILTERS


REFER TO AMPHENOL
CATALOGUE FOR FILTER
PERFORMANCE CHARACTERISTICS

SOCKET








CODE "F" MOUNTING OPTION



PIN







NOTES:

1) MATERIALS: ALL MATERIALS ARE RoHS COMPLIANT.
   - SHELL: STEEL, TIN PLATED
   - CONTACTS: PHOSPHOR BRONZE, GOLD PLATED OVER 50µ" [1.27 MICRONS] NICKEL IN THE MATING AREA AND 100µ" [2.54 MICRONS] MIN. MATTE TIN ON THE TAILS.
   - INSULATOR: ENGINEERING THERMOPLASTIC, GLASS REINFORCED, UL FLAMMABILITY RATING 94V–0, COLOUR: BLACK
   - BOARDLOCK: COPPER ALLOY, TIN PLATED
   - MOUNTING HARDWARE, STEEL OR COPPER ALLOY, TIN OR NICKEL PLATED.
2) CONTACT RESISTANCE: 15 MILLIOHMS MAXIMUM
3) INSULATION RESISTANCE: 3000 MEGOHMS MINIMUM
4) CURRENT RATING: 5 AMPS MAXIMUM
5) OPERATING TEMPERATURE: –40°C TO 85°C
6) GENERAL TOLERANCE ±.005 [0.13] UNLESS INDICATED OTHERWISE

SIZE	STYLE	A±.015 [0.38]	B±.005 [0.13]	C±.005 [0.13]	D±.005 [0.13]	E BSC.
E09	PIN	1.213 [30.81]	-----	.666 [16.92]	.984 [24.99]	.432 [10.97]
	SOCKET		.643 [16.33]	-----		
A15	PIN	1.541 [39.14]	-----	.994 [25.25]	1.312 [33.32]	.756 [19.20]
	SOCKET		.971 [24.66]	-----		
B25	PIN	2.088 [53.04]	-----	1.534 [38.96]	1.852 [47.04]	1.304 [33.12]
	SOCKET		1.511 [38.38]	-----		
C37	PIN	2.729 [69.32]	-----	2.182 [55.42]	2.500 [63.50]	1.956 [49.68]
	SOCKET		2.159 [54.84]	-----		

DRAWN K. LAMBIE	DATE SEP26/05	Amphenol Canada Corp.
DESIGNED		FCE17 SERIES FILTERED D–SUB CONNECTOR, PIN & SOCKET, RIGHT ANGLE .590 [14.99] F/P, PLASTIC BRACKET & BOARDLOCK, RoHS COMPLIANT
CHECKED		
I. E. APPRD.		
Q. A. APPRD.		
DWG. APPRD.		
ENG. REL. NO.		DWG C — DRAWING NO. P–FCE17–XXXXC–XX0X — REV. F
REF. EAR 12835		
DIMENSIONS ARE IN INCHES [mm]	CODE ID. NO. 03554	SCALE 2/1 — WT. ----- — SURF. ----- — SHEET 1 OF 1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

Downloaded from Arrow.com.