molex



**Part Number :** 919991284
**Product Description :** Appli-Mate RAST 5 Header, Vertical, 4 Circuits, Tin (Sn) Plating, Position Keys 2a, 3a, 3b & 4b, Code Keys 01c, d20, 03c & d40, Latches Between Circuits 1 & 2 and 3 & 4, PCB Polarization A, Glow-Wire Capable
**Series Number :** 91999
**Status :** Active
**Product Category :** PCB Headers and Receptacles
**Engineering Part Number :** WITH ZYTEL RM

## Documents and Resources

### Drawings

919991284_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

### Specifications

PK-90858-001-001.pdf

PS-99020-0037-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Compliant with Exemption 44; 33 |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |

Downloaded from Arrow.com.

| | |
|---|---|
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | PCB Headers and Receptacles |
| Series | 91999 |
| Description | Appli-Mate RAST 5 Header, Vertical, 4 Circuits, Tin (Sn) Plating, Position Keys 2a, 3a, 3b & 4b, Code Keys 01c, d20, 03c & d40, Latches Between Circuits 1 & 2 and 3 & 4, PCB Polarization A, Glow-Wire Capable |
| Application | Wire-to-Board |
| Comments | This Molex product is manufactured from material that has the following ratings, tested by independent agencies: a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12 and hence complies with the |

Downloaded from Arrow.com.

| | |
|---|---|
| | requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options. |
| Component Type | PCB Header |
| Product Name | RAST 5 |
| UPC | 822350968027 |

**Agency**

| | |
|---|---|
| CSA | LR19980 |
| UL | E29179 |

**Electrical**

| | |
|---|---|
| Current - Maximum per Contact | 16.0A |
| Voltage - Maximum | 250V AC |

**Physical**

| | |
|---|---|
| Breakaway | No |
| Circuits (Loaded) | 4 |
| Circuits (maximum) | 4 |
| Color - Resin | Natural |
| Durability (mating cycles max) | 10 |
| First Mate / Last Break | No |

Downloaded from Arrow.com.

| | |
|---|---|
| Gender | Male |
| Glow-Wire Capable | Yes |
| Guide to Mating Part | No |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Nylon |
| Mounting Style | Through Hole |
| Net Weight | 4.374/g |
| Number of Rows | 1 |
| Orientation | Vertical |
| Packaging Type | Bag |
| PCB Locator | Yes |
| PCB Retention | No |
| PCB Thickness - Recommended | 1.50mm |
| PC Tail Length | 3.50mm |
| Pitch - Mating Interface | 5.00mm |
| Pitch - Termination Interface | 5.00mm |
| Plating min - Mating | 3.000µm |
| Plating min - Termination | 3.000µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Shrouded | Shrouded |
| Stackable | No |
| Temperature Range - Operating | -20° to +120°C |
| Termination Interface Style | Through Hole |

**Solder Process Data**

| | |
|---|---|
| Max-Duration | 5 |
| Lead-Free Process Capability | WAVE |
| Max-Cycle | 1 |
| Max-Temp | 260 |

Downloaded from Arrow.com.

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| Appli-Mate RAST 5 IDT Housings | 91778 |
| Appli-Mate RAST 5 IDT Housings | 91779 |
| 5.00mm Pitch Appli-Mate RAST 5 IDT Connector System Female Receptacles | 91954 |

### Use with Part(s)

| Description | Part Number |
|---|---|
| Use With | RAST Standard Interface |

---

## Application Tooling

## Global

| Description | Part Number |
|---|---|
| RAST 5 Power Semi-Automatic IDC Machine | 2166580200 |

---



Downloaded from Arrow.com.