
REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
01	–	CUSTOMER DRAWING	–	–	–
02	–	CHANGED VOLTAGE FROM 150V TO 250V	19JAN22	MRF	DR








ILLUSTRATION: COMPLETE KIT





PANEL CUTOUT

NOTES:

1) CONTACT BARREL RANGE: 20AWG TO 22AWG
2) RECOMMENDED CRIMP TOOLS:
   HAND CRIMPER: MFX–3959
   PNEUMATIC CRIMPER: MFX–3960
3) EXTRACTION TOOL: QXRT20
4) MATERIALS:
   HOUSING BODY: ZINC DIE CAST, NICKEL PLATED
   INSULATION INSERT: PA66, UL94/V–0
   CONTACT: BRASS, GOLD FLASH PLATED
   SEAL AND O–RING: NBR (NITRILE BUTADIENE RUBBER)
5) ELECTRICAL DATA:
   a) CURRENT (MAX): 7.5A
   b) VOLTAGE (MAX): 250V AC/DC
   c) INSULATION RESISTANCE (MIN): 5000M OHMS
   d) TEST VOLTAGE (BETWEEN CONTACTS): 1500V
6) TECHNICAL DATA:
   a) TEMPERATURE RANGE: –40°C TO 105°C
   b) PROTECTION: IP67 (MATED CONDITION)
   c) MATING CYCLES: >500
   d) VIBRATION RESISTANCE PER MIL–STD–202 METHOD 204
   e) THERMAL SHOCK PER MIL–STD–202 METHOD 207
   f) 48 HOUR SALT SPRAY PER MIL–STD–202 METHOD 101
7) RoHS COMPLIANT

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
10	MP20W23F	CONTACT, PIN, SIZE 20	2
1	RT0W71210PNH	CONNECTOR	1

MATERIALS LIST

UNLESS OTHERWISE SPECIFIED
1) All dimensions are in metric(mm).
2) Tolerances are as follows:
1 PL DEC ±0.30 | Fractions ±1/64
2 PL DEC ±0.15 | Angles ±1°
3 PL DEC ±0.08
3) Note reference = X

MATERIAL SPECIFICATIONS:

PROCESS SPECIFICATIONS:

NEXT ASS'Y:

SIGNATURES		DATE
DRAWN:	MRF	10SEP13
CHECKED:		
ENGINEER:		
APPROVAL:		
CUSTOMER:		

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

Amphenol

Sine Systems - www.amphenol-sine.com
44724 Morley Drive
Clinton Township, MI 48036

KIT, ECO-MATE

SIZE	TYPE	DWG NO:	REVISION
B	C-	RT0W71210PNH-K	02

SCALE: NONE SHEET 1 OF 1

TITLE: KIT, ECO-MATE
DWG NO:
REV: 02
SH: 1
OF: 1

Downloaded from Arrow.com.

ecomate® RM/RSSM/Aquarius™ - Contact Size 20 Options

Machined, Crimp Contacts				
Part Number		Contact Size (AWG)	Wire Range (mm²)	Plating
Male	Female			
MP20W23F	MS20W23F	22-20AWG	0.34-0.50 mm²	Gold Flash
MP20W23G5	MS20W23G5	22-20AWG	0.34-0.50 mm²	Gold 5µ"
MP20W23G10	MS20W23G10	22-20AWG	0.34-0.50 mm²	Gold 10µ"
MP20W23G15	MS20W23G15	22-20AWG	0.34-0.50 mm²	Gold 15µ"
MP20W23G30	MS20W23G30	22-20AWG	0.34-0.50 mm²	Gold 30µ"
MP24W23F	MS24W23F	26-24AWG	0.14-0.25 mm²	Gold Flash
MP24W23G5	MS24W23G5	26-24AWG	0.14-0.25 mm²	Gold 5µ"
MP24W23G10	MS24W23G10	26-24AWG	0.14-0.25 mm²	Gold 10µ"
MP24W23G15	MS24W23G15	26-24AWG	0.14-0.25 mm²	Gold 15µ"
MP24W23G30	MS24W23G30	26-24AWG	0.14-0.25 mm²	Gold 30µ"
MP28W23F	MS28W23F	30-28AWG	0.05-0.08 mm²	Gold Flash
MP28W23G5	MS28W23G5	30-28AWG	0.05-0.08 mm²	Gold 5µ"
MP28W23G10	MS28W23G10	30-28AWG	0.05-0.08 mm²	Gold 10µ"
MP28W23G15	MS28W23G15	30-28AWG	0.05-0.08 mm²	Gold 15µ"
MP28W23G30	MS28W23G30	30-28AWG	0.05-0.08 mm²	Gold 30µ"

Stamped & Formed , Crimp Contacts				
Part Number		Contact Size (AWG)	Wire Range (mm²)	Plating
Male	Female			
SP20W2F	SS20W2F	22-20AWG	0.34-0.50 mm²	Gold Flash
SP20W2G5	SS20W2G5	22-20AWG	0.34-0.50 mm²	Gold 5µ"
SP20W2G10	SS20W2G10	22-20AWG	0.34-0.50 mm²	Gold 10µ"
SP20W2G15	SS20W2G15	22-20AWG	0.34-0.50 mm²	Gold 15µ"
SP20W2G30	SS20W2G30	22-20AWG	0.34-0.50 mm²	Gold 30µ"
SP24W2F	SS24W2F	26-24AWG	0.14-0.25 mm²	Gold Flash
SP24W2G5	SS24W2G5	26-24AWG	0.14-0.25 mm²	Gold 5µ"
SP24W2G10	SS24W2G10	26-24AWG	0.14-0.25 mm²	Gold 10µ"
SP24W2G15	SS24W2G15	26-24AWG	0.14-0.25 mm²	Gold 15µ"
SP24W2G30	SS24W2G30	26-24AWG	0.14-0.25 mm²	Gold 30µ"
SP28W2F	SS28W2F	30-28AWG	0.05-0.08 mm²	Gold Flash
SP28W2G5	SS28W2G5	30-28AWG	0.05-0.08 mm²	Gold 5µ"
SP28W2G10	SS28W2G10	30-28AWG	0.05-0.08 mm²	Gold 10µ"
SP28W2G15	SS28W2G15	30-28AWG	0.05-0.08 mm²	Gold 15µ"
SP28W2G30	SS28W2G30	30-28AWG	0.05-0.08 mm²	Gold 30µ"

Machined, Tooling	
Part Number	Description
QXRT20	Contact Extraction Tool, #20 (Ø 1.0) Contact
MFX-3959	Hand Crimp Tool for Machined Contacts
MFX-3960	Pneumatic Crimp Tool for Machined Contact

Stamped & Formed, Tooling	
Part Number	Description
QXRT20	Contact Extraction Tool, #20 (Ø 1.0) Contact
MFX-3958	Hand Tool, Stamped & Formed Contact, Size 20, 20-28AWG
MFX-3957	Crimp Die for Stamped & Formed Contact

Plating Options, All	
Symbol	Plating
T	Tin Plated (for Stamped & Formed Contacts)
S	Silver Plated 5Um (for Machined Contacts)
F	Gold Plated
G5	Gold Plated (Thickness 5µ")
G10	Gold Plated (Thickness 10µ")
G15	Gold Plated (Thickness 15µ")
G30	Gold Plated (Thickness 30µ")

Misc Tooling, All	
Part Number	Description
CA-4020-59	Sealing Plug, Size 16 & 20

Standard Quantity Order Options	
Machined	Bulk Package, 500 Pieces
Stamped & Formed	Reel, 3000 Pieces

Downloaded from Arrow.com.