

# CGA4J2X7R1C105K125AD

TDK Item Description : CGA4J2X7R1C105KT\*\*B




Equivalent C2012X7R1C105K for Automotive

## Application & Main Feature

Automotive Grade ( Conductive Epoxy Application )

## Series

CGA4(2012) [EIA CC0805]



## Dimensions

L 2.00mm +/-0.25mm  
W 1.25mm +/-0.25mm  
T 1.25mm +/-0.25mm  
B 0.20mm Min.  
G 0.50mm Min.

## Temperature Characteristic

X7R (-55 to 125 degC +/-15%)

## Rated Voltage

1C (16Vdc)

## Capacitance

1uF

## Capacitance Tolerance

K (+/-10%)

## Dissipation Factor

5% Max.


## Insulation Resistance

100Mohm Min.


## AEC-Q200

Yes


## DC Bias Characteristic




## |Z|, ESR vs. Freq. Characteristics




## Temperature Characteristics



## Cap. vs. Freq. Characteristic



## Ripple Temperature Rise Characteristics



All specifications are subject to change without notice.

January 4, 2016