


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2003 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
J	—	P	LTR	DESCRIPTION	DATE
		O		RELEASED FJA0-0444-03	23JUL03
					AY
					KB



- JUMPER LENGTH "L" IS FROM 12.7 MIN. TO 609.6 MAX.
- RECOMMENDED THROUGH HOLE DIA DIMENSION FOR P.C.BOARD: $\phi 0.94 \pm 0.025$
THROUGH HOLE PITCH TOLERANCE: ± 0.127
- ANOTHER SPECIFICATION SHOULD BE ESTABLISHED
IN CASE OF DEVIATION FROM THIS SPECIFICATION.
- WHEN N IS GREATER THAN 31, PCN INSERTION IS SUBJECT TO HAVE DIFFICULTY.
- DIMENSIONS OF LEAD POSITION ARE FOOT OF LEAD.

- ジャンパー長さ"L"は、最小12.7から、最大609.6まで。
- プリント基板スルーホール径： $\phi 0.94 \pm 0.025$ また、
スルーホールピッチ公差は、 ± 0.127 である。(推奨)
- 本仕様から逸脱する場合は、必ず仕様打合わせを行うこと。
- N31以上製品は、プリント基板挿入性が悪い場合がある。
- リード位置寸法は、リード根元部寸法とする。

2.54	38.1	2	-	NOT AVAILABLE	-
			-	NOT AVAILABLE	-
			-	NOT AVAILABLE	-
			-	NOT AVAILABLE	-
			FSN-21.5A-2=JUMPER	4-1437137-9	A
P	L	N	PART NAME	PN	TYPE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
単位: 英	一般公差
MM	
	0 PLC $\pm$
	1 PLC $\pm$
	2 PLC $\pm$
	3 PLC $\pm$
	4 PLC $\pm$
	ANGLES $\pm$
MATERIAL	FINISH
材料	仕上

DWN	A.YAMAGUCHI	22JUL03
CHK	K.BETSUI	23JUL03
APVD	K.BETSUI	23JUL03
PRODUCT SPEC	製品規格	108-78002
APPLICATION SPEC	取付適用規格	
WEIGHT	-	

WIRE RANGE	抱合電線断面積	INSULATION DIA	被覆外径
tyco Tyco Electronics AMP K.K. Electronics Kawasaki, Japan			
NAME 名称			
FLEX STRIP JUMPER P2.54L38.1N2			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=1717660	
SCALE 尺度		SHEET 1 OF 1	REV 0