

LUMOTAST 16, emergency stop button, 2 NC + 1 NO, Gold, Flat quick-connect terminal 2.8 x 0.5 tin-plated, reset by rotating, arrows red



fields of application

➤ Measurement-control-regulation

➤ Electrical engineering

➤ Mechanical and system engineering

➤ Signalling systems

➤ Handheld terminals

➤ Industrial robots

➤ Model construction

special features

➤ Round mounting hole, diameter 16.2 mm

➤ Mounting depth: 18 mm

➤ Terminal: male quick-connect terminal 2.8 x 0.5 mm

➤ Solderability: lead-free soldering with maximum 280°C for 5 seconds

➤ Water jet protection class IP 65 and IP 67 on front



description

The LUMOTAST 16 emergency stop elements are equipped with up to 3 contacts. This means that, for example, 2 redundant contacts can be earmarked for safety applications, while a signaling contact triggers the position sensing. An additional safety factor for your application.


technical data

➤ general		direct links
Color of mushroom	red	➤ RAFI eCatalog
Legending color	red	
Collar color	yellow	
Collar shape	round	
Operating temperature, min.	-25 °C	
Operating temperature, max.	70 °C	
Storage temperature, min.	-40 °C	
Storage temperature, max.	80 °C	
illuminated	No	
Packaging	Box	
Packaging unit	10 pcs.	
net weight	13.4 g	
Operating life	30,000 cycles	
B10	50,000 cycles	
B10d	100,000 cycles	
Degree of protection, front side, according to DIN EN 60529	IP65 IP67	
UL Enclosure Type Rating front side	type 1	
Impact resistance IK	05 side 05 frontal	


MOQ order	10 pcs.
Pollution degree acc. to DIN EN 61010-1	Pollution degree 2
RoHS compliant	Yes
REACH compliant	Yes
> mounting diameters	
Outside dimension, length	29.6 mm
Outside dimension, width	29.6 mm
Outside dimension, height	40.6 mm
Mounting hole	16.2 mm
Mounting depth	18 mm
Installation height	22.6 mm
> mechanical data	
Actuation function	latching
Contact function	2 NC + 1 NO
Contact material	Gold
Resetting	by rotating
Fixing	Threaded ring
Solderability	Yes
Threaded ring torque, max.	0.8 Nm
Terminal on the rear	Flat quick-connect terminal 2.8 x 0.5 tin-plated
> electrical data	
Rated insulation voltage	250 V
Rated voltage, min.	0.02 V
Rated voltage, max.	30 V
Rated voltage, max. acc. to UL 60947	35 V DC / 100 mA
Voltage type	AC / DC
Rated operating voltage	0.02-30 V
Rated current, min.	0.001 A
Rated current, max.	0.1 A
Categories of use	AC-15 DC-13

drawings

Dimensioned drawing



Mounting hole drawing



Schematic diagram

