



**Part Number :** [2451320410](#)

**Product Description :** Micro-fit 3.0-to-Micro-Fit 3.0  
Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual  
Row, 1.0m Length, 4 Circuits, Black

**Series Number :** 245132

**Status :** Active

**Product Category :** Power and Signal Cable  
Assemblies

**Engineering Part Number :** 795161041



---

## Documents and Resources

### Drawings

[2451320410\\_sd.pdf](#)

[2014400111-PK.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)


[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Power and Signal Cable Assemblies
Series	245132
Description	Micro-fit 3.0-to-Micro-Fit 3.0 Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 1.0m Length, 4 Circuits, Black
Application	Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Micro-Fit 3.0 Both Ends
Product Name	Micro-Fit 3.0
Type	Overmolded Assembly
UPC	889056858472

### Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	300V AC

### Physical

Cable Length	1.0m
Circuits (Loaded)	4
Circuits (maximum)	4

Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	53.600/g
Number of Rows	2
Overmolded	Yes
Packaging Type	Bag
Pitch - Mating Interface	3.00mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 2464
Wire Size (AWG)	20

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Micro-Fit 3.0 Dual Row Plug Housings	<u>43020</u>
Micro-Fit 3.0 Dual Row Headers	<u>43045</u>
Micro-Fit 3.0 Dual Row Test Plugs	<u>44242</u>

---

This document was generated on May 22, 2026