

The Ezurio Mini NanoBlade Flex antenna features a flexible printed circuit board that supports WLAN applications. The flexible board can be embedded in space-sensitive applications where a curved housing does not provide a flat surface for antenna mounting. The antennas are specifically designed to be embedded inside devices for aesthetically pleasing integration.

1 Features and Benefits

- Dual-band frequency coverage
- RoHS Compliant (2011/65/EU)
- Flexible PCB for mounting in curved housing

Electrical Specifications		
Operating Frequency (MHz)	2400-2500	4900-5875
Peak Gain - Max (dBi)	2.8	3.4
Efficiency (%)	68	59
VSWR, Max	2:1	
Polarization	Vertical, Omnidirectional	
Nominal Impedance (ohms)	50	


Mechanical Specifications	
Dimensions - mm (in.)	36 x 12 x 0.1 (1.42 x 0.47 x 0.004)
Hazardous Materials Compliance	RoHS Compliant (2011/65/EU)
Operational Temperature, oC (oF)	-35 to +85 (-31 to +185)
Storage Temperature, oC (oF)	-40 to + 85 (-40 to +185)

2 Configuration


Part Number	Cable Length (Length x Diameter)	Connector	Connector Orientation
MAF95310	185 mm (7.28 in.) x 1.13 mm (0.044 in.)	IPEX U.FL	A
EMF2449A1-10UFL	100 mm (3.94 in.) x 1.13 mm (0.044 in.)	IPEX U.FL	A
EMF2449A1-10MH4L	100 mm (3.94 in.) x 1.13 mm (0.044 in.)	IPEX MHF4L	A
EMF2449A2-10MHF1	100 mm (3.94 in.) x 1.13 mm (0.044 in.)	MHF1	B

Note: This antenna is available in many connector and cable configurations. Contact us at 1-847-839-6925 or <http://www.ezurio.com/contact> for more information.


3 Mechanical Drawing – MHF1 Version




4 Mechanical Drawing – MHF4L Version




4.1 Return Loss



4.2 Radiation Patterns




2400 MHz




4.3 Radiation Patterns


2450 MHz



2500 MHz




4900 MHz




4.4 Radiation Patterns

5470 MHz



5875 MHz



5 Additional Information

Please contact your local sales representative or our support team for further assistance:

Headquarters	Ezurio 50 S. Main St. Suite 1100 Akron, OH 44308 USA
Website	http://www.ezurio.com
Technical Support	http://www.ezurio.com/resources/support
Sales Contact	http://www.ezurio.com/contact

Note: Information contained in this document is subject to change.

Ezurio's products are subject to standard [Terms & Conditions](#).

© Copyright 2024 Ezurio. All Rights Reserved. Any information furnished by Ezurio and its agents is believed to be accurate but cannot be guaranteed. All specifications are subject to change without notice. Responsibility for the use and application of Ezurio materials or products rests with the end user since Ezurio and its agents cannot be aware of all potential uses. Ezurio makes no warranties as to non-infringement nor as to the fitness, merchantability, or sustainability of any Ezurio materials or products for any specific or general uses. Ezurio or any of its affiliates or agents shall not be liable for incidental or consequential damages of any kind. All Ezurio products are sold pursuant to the Ezurio Terms and Conditions of Sale in effect from time to time, a copy of which will be furnished upon request. Nothing herein provides a license under any Ezurio or any third-party intellectual property right. Ezurio and its associated logos are trademarks owned by Ezurio and/or its affiliates.