C3225CH2E103J160AA

TDK Item Description : C3225CH2E103JT****


Lead Free | Halogen Free | REACH | RoHS COMPLIANT

Application & Main Feature

Commercial Grade (Mid Voltage (100 to 630V))

Series

C3225 [EIA CC1210]



Dimensions

L	3.20mm +/-0.4mm
W	2.50mm +/-0.3mm
T	1.60mm +/-0.2mm
B	0.20mm Min.
G	

Temperature Characteristic

CH (-25 to 85 degC 0+/-60ppm/degC)

Rated Voltage

2E (250Vdc)

Capacitance

10nF

Capacitance Tolerance

J (+/-5%)

Q Factor


1000 Min.


Insulation Resistance


10Gohm Min.


AEC-Q200

Not Applicable









Characterization Sheet (Multilayer Ceramic Chip Capacitors)

TDK

All specifications are subject to change without notice.

January 4, 2016

Downloaded from Arrow.com.