Ordering number : ENA1548A

CPH6020

RF Transistor
8V, 150mA, fT=16GHz, NPN Single CPH6

ON Semiconductor®
http://onsemi.com

Features

- Low-noise use : NF=1.2dB typ (f=1GHz)
- High cut-off frequency : f_T=16GHz typ (V_{CE}=5V)
- High gain : $|S21e|^2$=13.5dB typ (f=1GHz)

Specifications


Absolute Maximum Ratings at Ta=25°C

Parameter	Symbol	Conditions	Ratings	Unit
Collector-to- Base Voltage	V_{CBO}		15	V
Collector-to-Emitter Voltage	V_{CEO}		8	V
Emitter-to-Base Voltage	V_{EBO}		2	V
Collector Current	I_C		150	mA
Collector Dissipation	P_C	When mounted on ceramic substrate (250mm²×0.8mm)	700	mW
Junction Temperature	Tj		150	°C
Storage Temperature	Tstg		−55 to +150	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

Package Dimensions


unit : mm (typ)
7018A-002




Product & Package Information

- Package : CPH6
- JEITA, JEDEC : SC-74, SOT-26, SOT-457
- Minimum Packing Quantity : 3,000 pcs./reel


Packing Type: TL



Marking



Electrical Connection



Downloaded from Arrow.com.


Electrical Characteristics at Ta=25°C


Parameter	Symbol	Conditions	Ratings			Unit
			min	typ	max	
Collector Cutoff Current	I_{CBO}	V_{CB}=5V, I_E=0A			1.0	μA
Emitter Cutoff Current	I_{EBO}	V_{EB}=1V, I_C=0A			1.0	μA
DC Current Gain	h_{FE}	V_{CE}=5V, I_C=50mA	60		150	
Gain-Bandwidth Product	f_T	V_{CE}=5V, I_C=50mA	13	16		GHz
Forward Transfer Gain	$\|S21e\|^2$	V_{CE}=5V, I_C=50mA, f=1GHz	10	13.5		dB
Noise Figure	NF	V_{CE}=1V, I_C=10mA, f=1GHz		1.2	1.8	dB


Notre) Pay attention to handling since it is liable to be affected by static electricity due to the high-frequency process adopted.


Ordering Information

Device	Package	Shipping	memo
CPH6020-TL-E	CPH6	3,000pcs./reel	Pb Free














Downloaded from Arrow.com.











Downloaded from Arrow.com.


Embossed Taping Specification

CPH6020-TL-E

1. Packing Format


Package Name	Carrier Tape Type	Maximum Number of devices contained (pcs)			Packing format	
		Reel	Inner box	Outer box	Inner BOX (C-1)	Outer BOX (A-7)
CPH6	CPH6	3,000	15,000	90,000	5 reels contained Dimensions:mm (external) 183×72×185	6 inner boxes contained Dimensions:mm (external) 440×195×210

Packing method



Reel label


Reel label, Inner box label (unit:mm)



Type No.
LOT No.
Quantity
Origin

Outer box label

It is a label at the time of factory shipments. The form of a label may change in physical distribution process.




NOTE (1)
The LEAD FREE ※ description shows that the surface treatment of the terminal is lead free.


Label	JEITA Phase
LEAD FREE 3	JEITA Phase 3A
LEAD FREE 4	JEITA Phase 3

2. Taping configuration

2-1. Carrier tape size (unit:mm)



2-2. Device placement direction




Those with pin 1 index on the feed hole side·····TL


Downloaded from Arrow.com.

Outline Drawing

CPH6020-TL-E



Land Pattern Example



Downloaded from Arrow.com.

ON Semiconductor and the ON logo are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

Downloaded from Arrow.com.