

FCB-405-0622M

✓ ACTIVE

CII | CII FCB-405 Series

TE Internal #: 8-1617760-3

General Purpose Power Relay, DC, Polarized, Monostable, 4 Form C 4PDT-CO, 5 A Contact Rating, 28 VDC Coil Voltage, Socket Mount, CII FCB-405 Series

[View on TE.com >](#)



Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **General Purpose Power Relay**

Coil Magnetic System: **Polarized, Monostable**

Contact Arrangement: **4 Form C 4PDT-CO**

Current Type: **DC**

Contact Current Rating: **5 A**

Features

Product Type Features

Relay & Contactor Type	General Purpose Power Relay
------------------------	-----------------------------

Configuration Features

Coil Special Features	Coil Suppression Diode
Relay Options	Back EMF Suppression
Contact Arrangement	4 Form C 4PDT-CO

Electrical Characteristics

Coil Resistance	400 Ω
Contact Current Rating	5 A
Coil Voltage Rating	28 VDC

Body Features

Enclosure Type	Hermetically Sealed
----------------	---------------------

Contact Features

Contact Material	Silver Cadmium Oxide
Terminal Plating	Gold

Termination Features

Main Termination & Connection Type	Socket Pins
Coil Termination & Connection Type	Socket Pins



Mechanical Attachment

Product Mounting Feature Type	Mounting Brackets
Product Mount Type	Socket Mount

Usage Conditions

Operating Temperature Range	-70 – 125 °C[-94 – 257 °F]
Environmental Ambient Temperature (Max)	125 °C[257 °F]

Operation/Application

Vibration Resistance	30G's, 70 – 3000Hz
Shock Resistance	200G's, 6ms
Coil Magnetic System	Polarized, Monostable
Current Type	DC

Other

Contact Current Class	>2 – ≤5 A
-----------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Cadmium oxide (10% in Component Part) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 8-1617758-0 FCB-205-CX2	TE Part # 9-1617784-3 FCB-205-0118L=M83536/1-018L	TE Part # 5-1617786-1 FCB-205-0218M=M83536/2-018M	TE Part # 7-1617758-9 FCB-205-BZ4
TE Part # 2-1617758-6 FCB-205-0110M=M83536/1-010M	TE Part # 5-1617786-8 FCB-205-0227L=M83536/2-027L	TE Part # 6-1617772-1 FCB-205-AZ3=RELAY	TE Part # 4-1617758-7 FCB-205-0222M=M83536/2-022M
TE Part # 5-1617758-1 FCB-205-0225M=M83536/2-025M	TE Part # 3-1617758-4 FCB-205-0125L=M83536/1-025L	TE Part # 4-1617758-1 FCB-205-0210M=M83536/2-010M	


Also in the Series | CII FCB-405 Series

DC Relays(22)	Electromechanical Relays(22)	Plug-In Relays(6)


Customers Also Bought



TE Part #ABC06N-20S
IN-LINE PLUG




TE Part #SME410-A010401
SME410-A010401=SOCKET




TE Part #SMEL410-C010403
SMEL410-C010403=SOCKET



TE Part #SM2-7
STRING POT, 7.5 INCH RANGE



TE Part #6-1616998-6
K4001B1C1=CONTACTOR SPST 28
VDC




TE Part #2-1617754-1
FCA-410-1622M=M83536/16-022M




TE Part #3-1617805-3
TD230-5003P=TD AO50-
500SECM83726/30-5003P



TE Part #5-1617805-5
TD228-5001P=TDFO 5 SEC M83726
/28-5001P



TE Part #2-1617090-7
LS-7105 = LS RELAY



TE Part #2157235-1
ARINC RCPT,Sz2,150/150/34,CHRO

Documents

Product Drawings

FCB-405-0622M=M83536/6-022M

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_8-1617760-3_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_8-1617760-3_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_8-1617760-3_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



[5-1773450-5_sec5_FCB-405](#)

English