

## M12-SD-CC-CRIMP-8P-YCOD-F-STR-SHLD



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 861 2825
Specification	M12-SD-CC-CRIMP-8P-YCOD-F-STR-SHLD
HARTING eCatalogue	<a href="https://harting.com/21038612825">https://harting.com/21038612825</a>

### Identification

Category	Connectors
Series	Circular connectors M12
Identification	Power
Element	Cable connector Panel feed through
Specification	for rear mounting

### Version

Termination method	Crimp termination
Gender	Female
Shielding	Shielded
Number of contacts	8
Number of data contacts	4
Number of power contacts	4
Coding	Y-coding
Locking type	Screw locking PushPull
Details	Please order crimp contacts separately.
Details	For Fast Ethernet applications only

### Technical characteristics

Rated current	6 A
Rated voltage	50 V
Rated impulse voltage	1.5 kV

Page 1 / 3 | Creation date 2026-01-28 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany  
Phone +49 5772 47-97200 | [electronics@HARTING.com](mailto:electronics@HARTING.com) | [www.HARTING.com](http://www.HARTING.com)



Pushing Performance  
Since 1945

## Technical characteristics

Pollution degree	3
Rated current (data)	0.5 A
Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Limiting temperature	-40 ... +85 °C
Mating cycles	$\geq 500$
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	5.7 ... 8.8 mm
Isolation group	I ( $600 \leq \text{CTI}$ )

## Material properties

Material (insert)	Polyamide (PA)
Material (hood/housing)	Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Specifications	IEC 61076-2-113
UL / CSA	UL 2238 CYJV2.E302521
PROFINET	Yes

## Commercial data

Packaging size	1
Net weight	54.75 g
Country of origin	Romania



**Pushing Performance**  
Since 1945

## Commercial data

European customs tariff number	85366990
GTIN	5713140227415
eCl@ss	27440116 Circular connector (for field assembly)
ETIM	EC002635
UNSPSC 24.0	39121413