


## Product Highlights

- Operating temperature from -60°C to +200°C (-76°F to +392°F)
- ASD EN 6049-006
- BMS 13-81 Type 1
- DMS2379 Class 4, Type 4
- FAR Part 25
- Halogen-free
- Self-wrapping design
- Easy to apply and remove
- Ideal for reworking components without disconnecting them
- Tough fabric texture
- Water repellent



**ROUNDIT® 2000 NX** is a woven combination of Nomex® and PPS (polyphenylene sulfide). The Nomex®/PPS blend in a flat weave construction gives ROUNDIT 2000 NX a rugged yet smooth texture and appearance for high temperature bundling and abrasion resistance. This product is rated to +200°C (+392°F) and is non-halogenated.

ROUNDIT 2000 NX is ideal for commercial and defense aircraft applications due to its excellent abrasion resistance and halogen-free qualities.

ROUNDIT® products are tough, lightweight oversleeves used to bundle and protect cable assemblies, hoses and wire harnesses from chafing, cutting and abrading. The self-wrapping feature of ROUNDIT products allows for quick and easy application and removal of the product for assembly and maintenance. The product may also be applied or removed without disturbing connectors or fittings.

*Nomex is a registered trademark of E.I. DuPont de Nemours.*



As an added benefit, the patented ROUNDIT® Tool will help improve installation time and is designed to install ROUNDIT® products on cable and wire configurations.



Our manufacturing sites are certified ISO 9001, IATF 16949, or AS/EN 9100, ISO 14001 and ISO 45001 (Selected Sites)

# Performance Data – ROUNDIT® 2000 NX

Property		Test Method		Result
PHYSICAL				
Operating Temperature				-60°C (-76°F) to +200°C (392°F)
Flammability		F.A.R. Part 25 (60 s) F.A.R. Part 25 (12 s)		Pass Pass
Smoke Density		ASTM E-662 (flaming) prEN 2825B (non-flaming)		Pass
Toxicity		BSS7239 + prEN 2826B		Pass
Water Repellency		EN 6059 Part 305		Pass
MECHANICAL				
Abrasion resistance		EN 6059 Part 403		Pass
Dynamic cut-through		EN 6059 Part 405		Pass
Vibration		DO 160B		No damage to cable
CHEMICAL				
Fluid Resistance		EN 6059 Part 303	BMS 13-81 § 8.2	
Fuel	JP5 Jet A, ASTM D1655	✓	✓	Good resistance
Hydraulic Fluid	Skydrol MIL-PRF-5606 MIL-PRF-87257	✓	✓ ✓ ✓	Good resistance
Methyl Propyl Ketone	BMS11-9, Grade 1		✓	Good resistance
Isopropyl Alcohol	TT-I-735		✓	Good resistance
Synthetic Lubricant	MIL-PRF-23699	✓	✓	Good resistance
Mineral Lubricant	MIL-L-7870A	✓		Good resistance
De-Icing Fluid	MIL-A-8243D	✓	✓	Good resistance
Cleaning Products	MIL-C-87937, Type 1 Alkaline Detergent (pH 10.0 - 10.5)	✓	✓	Good resistance
Mold Growth		EN 6059 Part 306		Pass

All numeric performance data shows average or typical values. Please consult your sales representative for product drawings, test reports and OEM approvals.

## Product Specifications

Commercial Part Number	Recommended Application Range mm (in)		Max Weight g/m (lbs/ft)	Standard Packaging m (ft)
	Min Ø	Max Ø		
ROUNDIT 2000 NX 5-5	1 (1/32")	5 (3/16")	13 (0.009)	150 (492')
ROUNDIT 2000 NX 8-5	5 (3/16")	8 (5/16")	18 (0.012)	100 (328')
ROUNDIT 2000 NX 13-5	8 (5/16")	13 (1/2")	26 (0.017)	50 (164')
ROUNDIT 2000 NX 16-5	13 (1/2")	16 (5/8")	33 (0.022)	25 (82')
ROUNDIT 2000 NX 19-5	16 (5/8")	19 (3/4")	38 (0.026)	25 (82')
ROUNDIT 2000 NX 25-5	19 (3/4")	25 (1")	47 (0.032)	25 (82')
ROUNDIT 2000 NX 32-5	25 (1")	32 (1-1/4")	65 (0.044)	25 (82')
ROUNDIT 2000 NX 40-5	32 (1-1/4")	40 (1-1/2")	90 (0.060)	25 (82')

Nominal size is determined by wrapping product around a mandrel of a given size to obtain an overlap of between 45 and 135.

## Part Numbering System

Example	Product Name	Size	Color	Quantity
	ROUNDIT 2000 NX	5	5 (green)	150m



United States: (1) 800 926 2472 • México: (52) 442 101 8100 • Brazil: (55) 19 3116 1600  
EMEA: (33) 3 44 39 06 06 • Japan: (81) 45 330 0300 • China: (86) 21 6182 7560  
Southeast Asia: (66) 35 276 400 • Korea: (82) 44 861 6368 • India: (91) 124 4784565  
[www.systemsprotection.com](http://www.systemsprotection.com)



For informational purposes only. SP makes no warranties as to the accuracy or completeness of the information provided herein and disclaims any liability in connection with its use. SP's only obligations are those provided in its terms and conditions of sale for this product, and SP will not be liable for any damages, whether direct or indirect, arising out of the use or misuse of this product. Users should undertake their own evaluations to determine the suitability of the product for specific applications. ©2024 Systems Protection - A Tenneco Company, manufacturer of Bentley-Harris protection products.