



Part Number : [2175011114](#)
Product Description : Pre-Crimped Lead Micro-Lock
Plus 2.0 Female-to-Pigtail, Tin (Sn) Plating, 300.00mm
Length, 24 AWG, Black
Series Number : 217501
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings

- [2175011114 sd.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	217501
Description	Pre-Crimped Lead Micro-Lock Plus 2.0 Female-to-Pigtail, Tin (Sn) Plating, 300.00mm Length, 24 AWG, Black
Application	Signal, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Micro-Lock Plus Crimp Terminal
Product Name	Micro-Lock Plus
UPC	195842650763

Electrical

Voltage - Maximum	250V AC (RMS)/DC
-------------------	------------------

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin

Material - Resin	PVC
Net Weight	0.752/g
Number of Rows	1
Packaging Type	Bag
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 10002
Wire Size (AWG)	24

This document was generated on Sep 24, 2025