



Part Number : [5030912621](#)
Product Description : 2.00mm Pitch, iGrid PCB
Header, Dual Row, Vertical, Through Hole, Gold (Au)
Plating, Positive Lock, 26 Circuits, Tray, 3.20mm PC Tail
Length, Black, with PCB Locator
Series Number : 503091
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[5030912621 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[5030912621.dxf](#)

Specifications

[5016460000-A00.pdf](#)

[5016460000-A01.pdf](#)

[5030919200-SPK-200.pdf](#)

[5016460000-PS-000.pdf](#)

[5016461000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025) SCIP:bc5968db-5bed-458f-8beb-659ba1c3f73d
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	503091
Description	2.00mm Pitch, iGrid PCB Header, Dual Row, Vertical, Through Hole, Gold (Au) Plating, Positive Lock, 26 Circuits, Tray, 3.20mm PC Tail Length, Black, with PCB Locator
Application	Signal, Wire-to-Board
Component Type	PCB Header
Product Name	iGrid
UPC	800756916002

Agency

CSA	LR19980
-----	---------

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Breakaway	No
Circuits (Loaded)	26
Circuits (maximum)	26
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Polyamide
Net Weight	1100.520/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.20mm, 1.60mm
PC Tail Length	3.20mm
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.100µm
Plating min - Termination	0.100µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No

Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole
Unmated Height	12.00mm

Mates With / Use With

Mates with Part(s)

Description	Part Number
iGrid Dual Row Receptacle Housings	<u>501646</u>

This document was generated on Dec 26, 2025