

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622023000

Status:

Active

Overview:

Application Tooling

Description:

Daughter Card Signal Module Removal Tool

Documents:


RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Removal
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Press-Fit Extraction Tool
UPC	800756898322
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical	
Net Weight	603.000/g

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-622023000, TM-622018699



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207123 Series

Use With

N/A

Application Tooling Description	FAQ Product #
GbX I-Trac Right-Angle Daughtercard Module, 1.85mm by 3.70mm Pitch, Unguided, 11 Rows, 5 Columns, 110 Circuits	757101005
GbX I-Trac Right-Angle Daughtercard Module, 1.85mm by 3.70mm Pitch, Unguided, 11 Rows, 6 Columns, 132 Circuits	757101006
GbX I-Trac Right-Angle Daughtercard Module, 1.85mm by 3.70mm Pitch, Unguided, 11 Rows,	757101008

8 Columns, 176
Circuits
GbX I-Trac Right- 757101010
Angle Daughtercard
Module, 1.85mm
by 3.70mm Pitch,
Unguided, 11 Rows,
10 Columns, 220
Circuits
GbX I-Trac Right- 757103006
Angle Daughtercard
Module, 1.85mm by
3.70mm Pitch, Left
Guide, 11 Rows,
6 Columns, 132
Circuits, Lead-Free
GbX I-Trac Right- 757103010
Angle Daughtercard
Module, 1.85mm by
3.70mm Pitch, Left
Guide, 11 Rows,
10 Columns, 220
Circuits, Lead-Free
GbX I-Trac Right- 757103208
Angle Daughtercard
Module, 1.85mm by
3.70mm Pitch, Left
Guide, 11 Rows,
8 Columns, 176
Circuits, Lead-Free,
Polarization Key B
GbX I-Trac Right- 757105006
Angle Daughtercard
Module, 1.85mm by
3.70mm Pitch, Right
Guide, 11 Rows,
6 Columns, 132
Circuits
GbX I-Trac Right- 757105008
Angle Daughtercard
Module, 1.85mm by
3.70mm Pitch, Right
Guide, 11 Rows,
8 Columns, 176
Circuits
GbX I-Trac Right- 757105010
Angle Daughtercard
Module, 1.85mm by
3.70mm Pitch, Right
Guide, 11 Rows,
10 Columns, 220
Circuits
GbX I-Trac Right- 760201004
Angle Receptacle
Module, 1.85mm
by 3.70mm Pitch,
Unguided, 7 Row, 4
Columns, 56 Circuits,
Lead-Free
GbX I-Trac Right- 760201006
Angle Receptacle
Module, 1.85mm
by 3.70mm Pitch,
Unguided, 7 Row, 6

Columns, 84 Circuits, Lead-Free GbX I-Trac Right-Angle Receptacle Module, 1.85mm by 3.70mm Pitch, Unguided, 7 Row, 10 Columns, 140 Circuits, Lead-Free	<u>760201010</u>
GbX I-Trac Right-Angle Receptacle Module, 1.85mm by 3.70mm Pitch, Left Guide 7 Row, 4 Columns, 56 Circuits, Lead-Free	<u>760203004</u>
GbX I-Trac Right-Angle Receptacle Module, 1.85mm by 3.70mm Pitch, Left Guide 7 Row, 10 Columns, 140 Circuits, Lead-Free	<u>760203010</u>
GbX I-Trac Right-Angle Receptacle Module, 1.85mm by 3.70mm Pitch, Right Guide 7 Row, 4 Columns, 56 Circuits, Lead-Free	<u>760205004</u>
GbX I-Trac Right-Angle Receptacle Module, 1.85mm by 3.70mm Pitch, Right Guide 7 Row, 6 Columns, 84 Circuits, Lead-Free	<u>760205006</u>
GbX I-Trac Right-Angle Receptacle Module, 1.85mm by 3.70mm Pitch, Right Guide 7 Row, 10 Columns, 140 Circuits, Lead-Free	<u>760205010</u>

This document was generated on 11/23/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION