

WE RECOMMEND THESE CONNECTORS FOR OPTIMAL SERVICE LEVEL



- SHORT LEAD-TIMES
- LOW MOQs
- QUICK SAMPLING
- AVAILABLE AT DISTRIBUTION



76383-302LF
76383-303LF
76383-304LF
76383-305LF
76383-306LF
76383-307LF
76383-308LF
76383-309LF
76383-310LF




PLATING
3 = 0.76µm GOLD/GXT ON CONTACT AREA
2µm TIN MIN ON TAIL
1.27µm Ni MIN UNDERLAYER

RoHS COMPATIBLE
SEE NOTE 7

NUMBER OF POSITIONS

NOTES:

1. BODY MATERIAL: POLYESTER 30% GLASSFILLED COLOR BLUE, FLAME RETARDANT PER UL-94 V0.
2. CONTACT MATERIAL: PHOSPHOR BRONZE.
3. 15N MIN PIN RETENTION IN EITHER DIRECTION
4. 0.6 MAX PROTRUSION PERMITTED AT 4 PLACES
5. PACKAGING :
 - POLYBAGS FROM 2 x 02 TO 2 x 06 POSITIONS
 - TUBE FROM 2 x 07 TO 2 x 36 POSITIONS
6. TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm
7. RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004
8. THIS PART SERIES IS NOT INITIALLY INTENDED FOR AUTOMOTIVE APPLICATIONS. ADDITIONAL FEES ARE CHARGEABLE FOR ANY ADDITIONAL QUALIFICATION AND TEST REPORTS PERFORMED OUTSIDE THE SCOPE OF THE STANDARD PRODUCT SPECIFICATIONS.
9. UNLESS OTHERWISE APPROVED BY AMPHENOL, ALL PARTS AND COMPONENTS ARE DESIGNED & BUILT ACCORDING TO AMPHENOL'S SPECIFICATIONS WHICH ARE SUBJECT TO CHANGE WITHOUT NOTICE.



mat'l. code SEE NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family DUBOX	
ltr	ecn no	dr	date	tolerances unless otherwise specified						title	
M	F10-0043	LMU	10.05.03	angles	linear	.X ±0.3				SHR. HEADER RA DR TMT	
N	F-21810	AMA	15.06.19			.XX ±0.15					
P	F-38327	DDE	20.09.11			.XXX ±0.05		scale 5:1			
R	F-54447	DDE	25.01.28	dr	D.LEGRAND	01.01.24				dwg no	
S	F-293257	DDE	26.06.12	engr	J.COMPAGNON	01.01.24				sheet 1 of 2	
				chr	J.COMPAGNON	01.01.24				76383	
L	F08-0147	YOV	08.04.14	appd	JF.NOTTEAU	01.01.24				size A	
sheet index		revision sheet		S	A					type CUSTOMER Drawing	
			1 2								
</											

EXTENDED RANGE

PRODUCT NUMBER

76383-YXXLF

RoHS COMPATIBLE, SEE NOTE 7

PLATING _____
(AS AVAILABLE)

NUMBER OF POSITIONS PER ROW : 02 TO 36


3=0.76µm GOLD/GXT ON CONTACT AREA

2µm MIN MATTE TIN ON TAIL

1.27µm Ni MIN UNDERPLATING

4=2µm MIN MATTE TIN FULL PLATED

1.27µm Ni MIN UNDERPLATING



mat'l. code				surface			tolerance		projection	product family		
SEE NOTES				ISO 1302	✓		ISO 406	ISO 1101		DUBOX		
ltr	ecn no	dr	date	tolerances unless otherwise specified					mm	title		
A	F-54447	DDE	25.01.28	angles	linear		.X	±0.3		SHR. HEADER RA DR TMT		
							.XX	±0.15				
							.XXX	±0.05	scale 5:1			
				dr		D.LEGRAND		01.01.24	Amphenol FCI	dwg no		
				enrg		J.COMPAGNON		01.01.24		sheet 2 of 2		
				chr		J.COMPAGNON		01.01.24		76383		
				appd		JF.NOTTEAU		01.01.24		type CUSTOMER Drawing		
sheet index	revision sheet											