



Search by part # or keyword

Products

Industries &
Solutions

Resources

TE Store

Sign In



Harnessing > Interconnect Devices > SolderSleeve Shield Terminators

B-150-13

B-150-13



Raychem

TE Internal #: **031307-000**

TE Internal Description: **B-150-13**

Alias #: **9-1190242-8**

Operating Temperature (Max) (°C): **125**

Expanded Inside Diameter (Min) : **15.1 mm**
[**.594 in**]

Recovered Inside Diameter (Max) : **13 mm**
[**.512 in**]

Pre-Installed Lead : **No**

Wire Temperature (Max) (°C): **85**

[Similar Products](#) | [Digital Datasheet](#)

Compatible Parts & Tooling

Free Shipping to select countries.
Exclusions apply. See complete details
at [TE Store FAQs](#)

QTY:

Extended Price:

We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

Documents

Features

Product Compliance

Product Drawings

B-150-13
 [B-150-13](#) English

Product
Specifications

B-150-XX (-S) and B-155-XX SolderSleeves
 [ENG_SS_RPIP-688-00_G_rpip_688_00_g.pdf](#)
English
Product Specification
 [ENG_SS_RT-1404_9.pdf](#) English

Product
Environmental
Compliance

REACH Substance Communication Document
 [ENG_PC_RSCD_Lead_HBCDD_Cadmium_1.pdf](#)
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Configuration
Features

Pre-Installed Lead : **No**

Dimensions

Expanded Inside Diameter (Min) : **15.1 mm [.594 in]**
Recovered Inside Diameter (Max) : **13 mm [.512 in]**

Feedback

Usage Conditions

Operating Temperature (Max) (°C): **125**

Wire Temperature (Max) (°C): **85**

EU RoHS Directive 2011/65/EU

Substances: Cd, Pb

This declaration covers EU Directive 2011/65/EU incl. Delegated Directive 2015/863/EU. The restrictions under 2015/863/EU apply as of 22 July 2021 for EEE categories 8 (medical devices) and 9 (monitoring and control equipment).

EU ELV Directive 2000/53/EC

Substances: Cd, Pb

China RoHS 2 Directive MIIT Order No 32, 2016

部件名称 (Component Name) 031307-000	有害物质 (Hazardous Substance)					
	铅 (Pb)	汞 (Hg)	镉 (Cd)	六价 铬 (Cr6)	多溴联 苯 (PBB)	多溴二苯 醚 (PBDE)
连接器系统 (Connector Systems)	X	O	X	O	O	O
本表格依据SJ/T 11364标准的规定编制。This table is compiled according to SJ/T 11364 standard.						
O: 表示该有害物质在该部件所有均质材料中的含量均在GB/T 26572标准规定的限量要求以下。 Indicates that the concentration of the hazardous substance in all homogeneous materials of the part is below the relevant threshold of the GB/T 26572 standard.						
X: 表示该有害物质至少在该部件的某一均质材料中的含量超出GB/T 26572标准规定的限量要求。 Indicates that the concentration of the hazardous substance in at least one homogeneous material of the part is above the relevant threshold of the GB/T 26572 standard.						
电子电气产品的环保使用期限依据SJ/T 11388标准的规定确定。 The EFUP value of EEP is defined according to SJ/T 11388 standard.						

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: **JUL 2019 (201)**
Candidate List Declared Against: **JUL 2019 (201)**
Cd (18% in Solder)
Pb (32% in Solder)
HBCDD (3% in Flux)

Halogen Content

Solder Process Capability

Not applicable for solder process capability

Statement of Compliance

[Statement of Compliance pdf](#)

Compliance Documents

There may be Environmental Compliance related documents on the [DOCUMENTATION Tab](#)

Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

TOP RESULTS ?

SOLDERSLEEVE SHIELD TERMINATORS	SOLDERSLEEVE SHIELD TERMINATORS	SOLDERSLEEVE SHIELD TERMINATORS	SOLDERSLEEVE SHIELD TERMINATORS
B-150-13	B-151-13	B-150-11-S	B-150-11
B-150-13	B-151-13	B-150-11-S	B-150-11
			
From In-Stock	In-Stock	Non-Stocked	From In-Stock
Operating Temperature (Max): 125 °C	Operating Temperature (Max): 125 °C	Operating Temperature (Max): 125 °C	Operating Temperature (Max): 125 °C
Expanded Inside Diameter (Min): 15.1 mm	Expanded Inside Diameter (Min): 15.1 mm	Expanded Inside Diameter (Min): 11.5 mm	Expanded Inside Diameter (Min): 11.5 mm
Recovered Inside Diameter (Max): 13 mm	Recovered Inside Diameter (Max): 7 mm	Recovered Inside Diameter (Max): 4 mm	Recovered Inside Diameter (Max): 10.8 mm
Pre-Installed Lead : No ...	Pre-Installed Lead : No ...	Pre-Installed Lead : No ...	Pre-Installed Lead : No ...

