

## 42U SmartRack 4-Post Mid-Depth Open Frame Rack, Expansion Version - no sides, doors or roof

MODEL NUMBER: **SR42BMDEXPNDR3**



### Description

The SR42BMDEXPNDR3 offers 36-inch (927-millimeter) depth opposed to the standard 42 inches (1050 millimeters).

The SR42BMDEXPNDR3 houses 3,000 pounds (1360.8 kilograms) of standard 19-inch rack equipment in 42U. It is an expansion model that comes without sides, doors or roof. The front and rear pairs of vertical rails have square mounting holes that are adjustable in quarter-inch increments from four to 28.75 inches. Adjustment is quick and an easy-view depth index ensures consistent rail placement without requiring time-consuming measurements. Each rack space within the enclosure is numbered for ready reference and supports tool-less button-mount 0U installation of up to four compatible PDUs and cable managers.

All components of the SR42BMDEXPNDR3 are grounded to the enclosure frame. Front and rear threaded grounding points are provided for connection to the facility earth ground.

To simplify deployment, the SR42BMDEXPNDR3 comes with preinstalled three-inch casters that enable it to be easily maneuvered into the desired location, where it can be secured by adjusting the preinstalled levelers. Note: The casters are intended for minor position adjustments and are not designed for moving the enclosure over long distances.

### Features

- Ships fully assembled for rapid deployment and roll into place on heavy-duty pre-installed 3" casters (casters are removable)
- Front and rear sets of equipment mounting rails adjust in 1/4" increments. Adjustment is quick and convenient. The easy-view depth index ensures consistent rail placement without requiring time-consuming measurements.
- Tool-less accessory mounting rails (2 rails per enclosure) include slots for quick installation of compatible PDUs and vertical cable managers. Mounting slots are arranged in an industry-standard pattern compatible with a wide variety of accessories. Each rail can accommodate two vertical PDUs or cable managers side-by-side (four items per enclosure).
- Enclosure includes mounting hardware of 50 pieces of M6 cage nuts and 50 pieces of M6 screws
- Textured powder coat finish for tough resistance to environmental concerns such as deployment in warehouses.
- Maximum usable internal depth of 31 inches/787 mm (front to rear rail).
- Weight ratings of 3000 lbs (1360.8 kgs) stationary and 3000 lbs (1360.8 kgs) rolling.
- Built in baying tabs allow premium open frame racks to be combined securely in rows. Center-to-center width can be set at 600mm or 24" to match standard data center floor tiles.

### Highlights

- 42U SmartRack Premium open frame rack (no sides, doors or roof)
- 36" (927mm) depth (with mounting depth increments from 4 to 28.75") and standard 24" (600mm) width
- 4 interior vertical posts with unthreaded square hole openings
- Ships fully assembled
- 3000 lbs (1360.8 kgs) stationary / 3000 lbs (1360.8 kgs) rolling load capacity
- Preinstalled heavy duty 3" casters and leveling feet
- Rolls through standard 7-ft. (2.13 m) doorway
- Includes 50 pieces of M6 cage nuts and 50 pieces of M6 screws (equipment mounting hardware)

### Package Includes

- SR42BMDEXPNDR3
- Mounting Hardware
- Owner's Manual



Powering Business Worldwide

TRIPP LITE  
SERIES

- Leveling feet extend to allow premium open frame racks to be positioned on uneven floors. Levelers are removable.
- Compact design allows the premium open frame racks to roll through standard height commercial doorways.
- Convenient grounding system. All components are grounded to the premium open frame rack structure which includes multiple connections for facility ground.
- Open top and bottom for cable access.
- Included stabilizing brackets are used for shipment and can be reattached at the bottom of the premium open frame rack on the inside or outside of the rack.
- Compatibility with all cable management accessories.

## Specifications

| OVERVIEW                          |                                  |
|-----------------------------------|----------------------------------|
| UPC Code                          | 037332175687                     |
| Device Compatibility              | Patch Panel; Network Switch; UPS |
| Rack Type                         | Open-Frame                       |
| PHYSICAL                          |                                  |
| Color                             | Black                            |
| Rack Height                       | 42U                              |
| Rack Depth                        | Mid                              |
| Maximum Device Depth (cm)         | 78.74                            |
| Maximum Device Depth (in.)        | 31                               |
| Maximum Device Depth (mm)         | 787                              |
| Minimum Device Depth (cm)         | 10.16                            |
| Minimum Device Depth (in.)        | 4                                |
| Minimum Device Depth (mm)         | 102                              |
| Shipping Dimensions (hwd / in.)   | 85.00 x 26.00 x 37.80            |
| Shipping Dimensions (hwd / cm)    | 215.90 x 66.04 x 96.01           |
| Shipping Weight (lbs.)            | 130.00                           |
| Shipping Weight (kg)              | 58.97                            |
| Unit Dimensions (hwd / in.)       | 79.500 x 23.630 x 36.000         |
| Unit Dimensions (hwd / cm)        | 201.93 x 60.02 x 91.44           |
| Unit Weight (lbs.)                | 94                               |
| Unit Weight (kg)                  | 42.64                            |
| Weight Capacity - Rolling (kg)    | 1,361                            |
| Weight Capacity - Rolling (lbs.)  | 3000                             |
| Weight Capacity - Stationary (kg) | 1,361                            |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                            |
|--------------------------------------|----------------------------|
| Weight Capacity - Stationary (lbs.)  | 3000                       |
| Number of Vertical Mounting Rails    | 4                          |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                            |
| Grounding Details                    | Front and Back door frames |
| Built-in Cable Management            | No                         |
| Extra Wide                           | No                         |
| Pre-Installed Casters                | Yes                        |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                            |
| Product Certifications               | UL 60950-1                 |
| Product Compliance                   | RoHS; CE (Europe); UKCA    |
| <b>WARRANTY &amp; SUPPORT</b>        |                            |
| Product Warranty Period (Worldwide)  | 5-year limited warranty    |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.