





OGA DIAGONAL: 20.44 [519.08]
VA DIAGONAL: 19.71 [500.74]
PA DIAGONAL: 18.58 [472.03]




(HID M)
EXII-7730HC
98-0003-2813-2
HID CONTROLLER
SOLDER SIDE

(HID D)
EXII-7740HC
98-0003-3065-8
HID CONTROLLER
SOLDER SIDE

(USB R)
EXII-7760UC
98-0003-2814-0
USB CONTROLLER
SOLDER SIDE



TOP LEVEL NUMBER	SKU 98 NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-8051-203	98-0003-2532-8	FFC	4.27" [108.46]	AG500	23655
17-8051-205	98-0003-2185-5	FFC	8.00" [203.20]	AG500	23655
17-8051-206	98-0003-2186-3	NOV	SEE DWG	AG500	23655
17-8051-221	98-0003-2537-7	SER	4.27" [108.46]	AG500	23655
17-8051-227	98-0003-2927-0	SER	8.00" [203.20]	AG500	23655
17-8051-218	98-0003-2535-1	USB R	4.27" [108.46]	AG500	23655
17-8051-226	98-0003-3114-4	USB R	8.00" [203.20]	AG500	23655
N/A	98-0003-3535-0	HID D	8.00" [203.20]	AG500	23655
N/A	98-0003-3199-5	HID M	8.00" [203.20]	AG500	23655
N/A	98-0003-3413-0	SER	6.00" [152.40]	AG500	23655
N/A	98-0003-3421-3	SER	6.00" [152.40]	WC100	34523
N/A	98-0003-3422-1	USB	6.00" [152.40]	WC100	34523
N/A	98-0003-3423-9	FFC	6.00" [152.40]	WC100	34523



NOTES:

1. WEIGHT OF GLASS IN GRAMS: 1005±10%
2. 5 PIN AMP CONNECTOR
LATCH STYLE HOUSING P/N: 487526-4
TIN CONTACTS P/N: 2-487406-4
HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	LR
2	LL
3	SHIELD
4	UL
5	UR

UNITS	INCHES [MM]
TOLERANCES UNLESS OTHERWISE SPECIFIED	
.X	±
.XX	±.03 [.76]
.XXX	±.015 [.38]
ANGLES	±1°



DO NOT SCALE DRAWING
SCALE 1 = 1

3M 3M TOUCH SYSTEMS
METHUEN, MA
USA
© COPYRIGHT 2005
THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE
3M COMPANY AND MAY NOT BE REPRODUCED
WITHOUT 3M WRITTEN PERMISSION OR USED OR
DISCLOSED FOR OTHER THAN 3M AUTHORIZED
PURPOSES.

DRAWN K. CROWLEY 9/05

10	REVISED PER CO 031907	7/10	SB
09	REVISED PER CO 031876	7/10	SB
08	REVISED PER CO 031738	6/10	MTD
REV	CHANGE NOTICE	DATE	DRW

MARKETING DRAWING
SCT32NN 19.71"

CAD FORMAT	AUTOCAD	SHEET	1 OF 1
SIZE	DOCUMENT NO.	REV	
C	28177-MKT	10	