
Data sheet

IE-BI-RJ45-FJ-P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



RJ45 inserts for plug-in connectors ver.1 / 4 / 5 / 14,
HDC and junction boxes IE-OM...; IE-OP...; IE-CC...

General ordering data

Version	RJ45 insert socket, Connector for base, PROFINET
Order No.	1963830000
Type	IE-BI-RJ45-FJ-P
GTIN (EAN)	4032248646159
Qty.	10 items

Downloaded from Arrow.com.

Data sheet

IE-BI-RJ45-FJ-P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E316369

Dimensions and weights

Net weight	16 g

Temperatures

Storage temperature		Operating temperature	-40 °C...70 °C
Installation temperature		Humidity	0...93 % rel. humidity

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Product type	RJ45 insert socket	Protection degree	IP67 with housing
Insert type	Insert data SteadyTec		

General data

Connection 1	RJ45	Connection 2	IDC
Description of article	Connector for base	Wiring	PROFINET
Colour	Miscellaneous	Shock resistance acc. to IEC 60512-6-3	250 ms-2
Vibration resistance acc. to IEC 60512-6-4	50 ms-2 sinusoidal (9... 500 Hz)	Humidity	0...93 % rel. humidity
Housing main material	Zinc diecast	Insulation cross-section, min.	0.85 mm
Insulation cross-section, max.	1.6 mm	Category	Cat.5 (ISO/IEC 11801)
Contact material	Spring steel, Ni 1.2 µm	Contact surface	Gold over Nickel, Au ≥ 0.8 µm
Connection diameter, solid	0.4...0.64 mm	Conductor connection cross-section, solid (AWG)	AWG 24...AWG 22
Connection diameter, flexible	0.48...0.76 mm	Conductor connection cross-section, flexible (AWG)	AWG 26...AWG 22
Shielding	360° all-round enclosure, FS 2.8 Ground connection for equipotential bonding	Protection degree	IP67 with housing
Plugging cycles	750	Ability to reconnect	≥ 10 cycles for AWG 23-26, ≥ 4 cycles for AWG 22

Electrical properties

Contact resistance	≤ 20 mΩ	Dielectric strength, contact / shield	≥ 1500 V AC/DC
Dielectric strength, contact / contact	≥ 1000 V AC/DC	Insulation resistance	500 MΩ
Current-carrying capacity at 50 °C	1 A	PoE / PoE+	conforming to IEEE 802.3bt

Downloaded from Arrow.com.

Weidmüller

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

General standards

Certificate No. (DNV)	TAA000022B	Connector standard	IEC 60603-7-51
UL standard for communication accessories	UL 1863	Application-specific communication cable facilities	PROFINET installation instructions
IP protection classes	IEC 60529	Certificate no. (cULus)	E316369

Important note

Product information	RJ45 inserts for plug-in connectors ver.1 / 4 / 5 / 14, HDC and junction boxes IE-OM...; IE-OP...; IE-CC...

Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

Downloaded from Arrow.com.

Weidmüller

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Printing



Downloaded from Arrow.com.