

# 3-STATE Quad Buffers

## MM74HC125, MM74HC126

### General Description


The MM74HC125 and MM74HC126 are general purpose 3-STATE high speed non-inverting buffers utilizing advanced silicon-gate CMOS technology. They have high drive current outputs which enable high speed operation even when driving large bus capacitances. These circuits possess the low power dissipation of CMOS circuitry, yet have speeds comparable to low power Schottky TTL circuits. Both circuits are capable of driving up to 15 low power Schottky inputs.

The MM74HC125 require the 3-STATE control input C to be taken high to put the output into the high impedance condition, whereas the MM74HC126 require the control input to be low to put the output into high impedance.


All inputs are protected from damage due to static discharge by diodes to VCC and ground.

### Features


- Typical Propagation Delay: 13 ns
- Wide Operating Voltage Range: 2 V – 6 V
- Low Input Current: 1  $\mu$ A Maximum
- Low Quiescent Current: 160  $\mu$ A maximum (74HC Series)
- Fanout of 15 LS-TTL Loads
- These Devices are Pb-Free, Halide Free and are RoHS Compliant



SOIC-14  
CASE 751A-03




SOIC-14  
CASE 751EF




TSSOP-14 WB  
CASE 948G

### MARKING DIAGRAM



SOIC-14



TSSOP-14 WB


XXXXX = Specific Device Code  
A = Assembly Location  
WL, L = Wafer Lot  
Y = Year  
WW, W = Work Week

### ORDERING INFORMATION


See detailed ordering and shipping information on page 6 of this data sheet.

# MM74HC125, MM74HC126

## Connection Diagram



Top View (MM74HC125)



Top View (MM74HC126)

Figure 1. Pin Assignments for SOIC and TSSOP

TRUTH TABLE (MM74HC125)

| Inputs |   | Output |
|--------|---|--------|
| A      | C | Y      |
| H      | L | H      |
| L      | L | L      |
| X      | H | Z      |

TRUTH TABLE (MM74HC126)

| Inputs |   | Output |
|--------|---|--------|
| A      | C | Y      |
| H      | H | H      |
| L      | H | L      |
| X      | L | Z      |

# MM74HC125, MM74HC126

## ABSOLUTE MAXIMUM RATINGS (Note 1)

| Symbol           | Parameter                               | Rating                   |
|------------------|-----------------------------------------|--------------------------|
| $V_{CC}$         | Supply Voltage                          | −0.5 to +6.5 V           |
| $V_{IN}$         | DC Input Voltage                        | −0.5 to $V_{CC} + 0.5$ V |
| $V_{OUT}$        | DC Output Voltage                       | −0.5 to $V_{CC} + 0.5$ V |
| $I_{IK}, I_{OK}$ | Clamp Diode Current                     | ±20 mA                   |
| $I_{OUT}$        | DC Output Current, per Pin              | 35 mA                    |
| $I_{CC}$         | DC $V_{CC}$ or GND Current, per Pin     | ±70 mA                   |
| $T_{STG}$        | Storage Temperature Range               | −65°C to +150°C          |
| $P_D$            | Power Dissipation<br>SOIC<br>TSSOP      | 1077 mW<br>833 mW        |
| $T_L$            | Lead Temperature (Soldering 10 Seconds) | 260°C                    |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Unless otherwise specified all voltages are referenced to ground.

## RECOMMENDED OPERATING CONDITIONS

| Symbol            | Parameter                   | Min              | Max      | Unit |
|-------------------|-----------------------------|------------------|----------|------|
| $V_{CC}$          | Supply Voltage              | 2                | 6        | V    |
| $V_{IN}, V_{OUT}$ | DC Input or Output Voltage  | 0                | $V_{CC}$ | V    |
| $T_A$             | Operating Temperature Range | −55              | +125     | °C   |
| $t_r, t_f$        | Input Rise or Fall Time     | $V_{CC} = 2.0$ V |          | ns   |
|                   |                             | $V_{CC} = 4.5$ V |          | ns   |
|                   |                             | $V_{CC} = 6.0$ V |          | ns   |

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

# MM74HC125, MM74HC126

## DC CHARACTERISTICS (Note 2)

| Symbol          | Parameter                              | Conditions                                                                                                                       | V <sub>CC</sub> (V) | T <sub>A</sub> = 25°C |                   | T <sub>A</sub> = -40°C<br>to 85°C | T <sub>A</sub> = -55°C<br>to 125°C | Unit |
|-----------------|----------------------------------------|----------------------------------------------------------------------------------------------------------------------------------|---------------------|-----------------------|-------------------|-----------------------------------|------------------------------------|------|
|                 |                                        |                                                                                                                                  |                     | Typ                   | Guaranteed Limits |                                   |                                    |      |
| V <sub>IH</sub> | Minimum HIGH Level Input Voltage       |                                                                                                                                  | 2.0                 | –                     | 1.5               | 1.5                               | 1.5                                | V    |
|                 |                                        |                                                                                                                                  | 4.5                 | –                     | 3.15              | 3.15                              | 3.15                               |      |
|                 |                                        |                                                                                                                                  | 6.0                 | –                     | 4.2               | 4.2                               | 4.2                                |      |
| V <sub>IL</sub> | Maximum LOW Level Input Voltage        |                                                                                                                                  | 2.0                 | –                     | 0.5               | 0.5                               | 0.5                                | V    |
|                 |                                        |                                                                                                                                  | 4.5                 | –                     | 1.35              | 1.35                              | 1.35                               |      |
|                 |                                        |                                                                                                                                  | 6.0                 | –                     | 1.8               | 1.8                               | 1.8                                |      |
| V <sub>OH</sub> | Minimum HIGH Level Output Voltage      | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub> ,<br> I <sub>OUT</sub>   ≤ 20 μA                                            | 2.0                 | 2.0                   | 1.9               | 1.9                               | 1.9                                | V    |
|                 |                                        |                                                                                                                                  | 4.5                 | 4.5                   | 4.4               | 4.4                               | 4.4                                |      |
|                 |                                        |                                                                                                                                  | 6.0                 | 6.0                   | 5.9               | 5.9                               | 5.9                                |      |
|                 |                                        | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub> ,<br> I <sub>OUT</sub>   ≤ 6.0 mA                                           | 4.5                 | 4.2                   | 3.98              | 3.84                              | 3.7                                |      |
|                 |                                        | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub> ,<br> I <sub>OUT</sub>   ≤ 7.8 mA                                           | 6.0                 | 5.7                   | 5.48              | 5.34                              | 5.2                                |      |
| V <sub>OL</sub> | Maximum LOW Level Output Voltage       | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub> ,<br> I <sub>OUT</sub>   ≤ 20 μA                                            | 2.0                 | 0                     | 0.1               | 0.1                               | 0.1                                | V    |
|                 |                                        |                                                                                                                                  | 4.5                 | 0                     | 0.1               | 0.1                               | 0.1                                |      |
|                 |                                        |                                                                                                                                  | 6.0                 | 0                     | 0.1               | 0.1                               | 0.1                                |      |
|                 |                                        | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub> ,<br> I <sub>OUT</sub>   ≤ 6.0 mA                                           | 4.5                 | 0.2                   | 0.26              | 0.33                              | 0.4                                |      |
|                 |                                        | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub> ,<br> I <sub>OUT</sub>   ≤ 7.8 mA                                           | 6.0                 | 0.2                   | 0.26              | 0.33                              | 0.4                                |      |
| I <sub>OZ</sub> | Maximum 3–STATE Output Leakage Current | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub> ,<br>V <sub>OUT</sub> = V <sub>CC</sub> or GND<br>C <sub>n</sub> = Disabled | 6.0                 | –                     | ±0.5              | ±5                                | ±10                                | μA   |
| I <sub>IN</sub> | Maximum Input Current                  | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                                                         | 6.0                 | –                     | ±0.1              | ±1.0                              | ±1.0                               | μA   |
| I <sub>CC</sub> | Maximum Quiescent Supply Current       | V <sub>IN</sub> = V <sub>CC</sub> or GND,<br>I <sub>OUT</sub> = 0 μA                                                             | 6.0                 | –                     | 8.0               | 80                                | 160                                | μA   |

2. For a power supply of 5 V ±10% the worst case output voltages (V<sub>OH</sub>, and V<sub>OL</sub>) occur for HC at 4.5 V. Thus the 4.5 V values should be used when designing with this supply. Worst case V<sub>IH</sub> and V<sub>IL</sub> occur at V<sub>CC</sub> = 5.5 V and 4.5 V respectively. (The V<sub>IH</sub> value at 5.5 V is 3.85 V.) The worst case leakage current (I<sub>IN</sub>, I<sub>CC</sub>, and I<sub>OZ</sub>) occur for CMOS at the higher voltage and so the 6.0 V values should be used.



# MM74HC125, MM74HC126

## AC CHARACTERISTICS ( $V_{CC} = 5\text{ V}$ , $T_A = 25^\circ\text{C}$ , $C_L = 45\text{ pF}$ , $t_r = t_f = 6\text{ ns}$ )

| Symbol                | Parameter                                   | Conditions                                     | Typ | Guaranteed Limit | Unit |
|-----------------------|---------------------------------------------|------------------------------------------------|-----|------------------|------|
| $t_{PHL}$ , $t_{PLH}$ | Maximum Propagation Delay Time              |                                                | 13  | 18               | ns   |
| $t_{PZH}$             | Maximum Output Enable Time to HIGH Level    | $R_L = 1\text{ k}\Omega$                       | 13  | 25               | ns   |
| $t_{PHZ}$             | Maximum Output Disable Time from HIGH Level | $R_L = 1\text{ k}\Omega$ , $C_L = 5\text{ pF}$ | 17  | 25               | ns   |
| $t_{PZL}$             | Maximum Output Enable Time to LOW Level     | $R_L = 1\text{ k}\Omega$                       | 18  | 25               | ns   |
| $t_{PLZ}$             | Maximum Output Disable Time from LOW Level  | $R_L = 1\text{ k}\Omega$ , $C_L = 5\text{ pF}$ | 13  | 25               | ns   |

## AC CHARACTERISTICS ( $V_{CC} = 2.0\text{ V}$ to $6.0\text{ V}$ , $C_L = 50\text{ pF}$ , $t_r = t_f = 6\text{ ns}$ (unless otherwise specified))

| Symbol                              | Parameter                                         | V <sub>CC</sub> (V) | Conditions                                        | T <sub>A</sub> = 25°C |                   | T <sub>A</sub> = −40°C to 85°C | T <sub>A</sub> = −55°C to 125°C | Unit |
|-------------------------------------|---------------------------------------------------|---------------------|---------------------------------------------------|-----------------------|-------------------|--------------------------------|---------------------------------|------|
|                                     |                                                   |                     |                                                   | Typ                   | Guaranteed Limits |                                |                                 |      |
| t <sub>PHL</sub> , t <sub>PLH</sub> | Maximum Propagation Delay Time                    | 2.0                 |                                                   | 40                    | 100               | 125                            | 150                             | ns   |
|                                     |                                                   | 4.5                 |                                                   | 14                    | 20                | 25                             | 30                              |      |
|                                     |                                                   | 6.0                 |                                                   | 12                    | 17                | 21                             | 25                              |      |
| t <sub>PLH</sub> , t <sub>PHL</sub> | Maximum Propagation Delay Time                    | 2.0                 | C <sub>L</sub> = 150 pF,                          | 35                    | 130               | 163                            | 195                             | ns   |
|                                     |                                                   | 4.5                 |                                                   | 14                    | 26                | 33                             | 39                              |      |
|                                     |                                                   | 6.0                 |                                                   | 12                    | 22                | 28                             | 39                              |      |
| t <sub>PZH</sub> , t <sub>PZL</sub> | Maximum Output Enable Time                        | 2.0                 | R <sub>L</sub> = 1 kΩ                             | 25                    | 125               | 156                            | 188                             | ns   |
|                                     |                                                   | 4.5                 |                                                   | 14                    | 25                | 31                             | 38                              |      |
|                                     |                                                   | 6.0                 |                                                   | 12                    | 21                | 26                             | 31                              |      |
| t <sub>PHZ</sub> , t <sub>PLZ</sub> | Maximum Output Disable Time                       | 2.0                 | R <sub>L</sub> = 1 kΩ                             | 25                    | 125               | 156                            | 188                             | ns   |
|                                     |                                                   | 4.5                 |                                                   | 14                    | 25                | 31                             | 38                              |      |
|                                     |                                                   | 6.0                 |                                                   | 12                    | 21                | 26                             | 31                              |      |
| t <sub>PZL</sub> , t <sub>PZH</sub> | Maximum Output Enable Time                        | 2.0                 | C <sub>L</sub> = 150 pF,<br>R <sub>L</sub> = 1 kΩ | 35                    | 140               | 175                            | 210                             | ns   |
|                                     |                                                   | 4.5                 |                                                   | 15                    | 28                | 35                             | 42                              |      |
|                                     |                                                   | 6.0                 |                                                   | 13                    | 24                | 30                             | 36                              |      |
| t <sub>TLH</sub> , t <sub>THL</sub> | Maximum Output Rise and Fall Time                 | 2.0                 | C <sub>L</sub> = 50 pF                            | 30                    | 60                | 75                             | 90                              | ns   |
|                                     |                                                   | 4.5                 |                                                   | 7                     | 12                | 15                             | 18                              |      |
|                                     |                                                   | 6.0                 |                                                   | 6                     | 10                | 13                             | 15                              |      |
| C <sub>IN</sub>                     | Input Capacitance                                 |                     |                                                   | 5                     | 10                | 10                             | 10                              | pF   |
| C <sub>OUT</sub>                    | Output Capacitance Outputs                        |                     |                                                   | 15                    | 20                | 20                             | 20                              | pF   |
| C <sub>PD</sub>                     | Power Dissipation Capacitance (per gate) (Note 3) |                     | Enabled                                           | 45                    | –                 | –                              | –                               | pF   |
|                                     |                                                   |                     | Disabled                                          | 6                     | –                 | –                              | –                               |      |

3.  $C_{PD}$  determines the no load dynamic power consumption,  $P_D = C_{PD} V_{CC}^2 f + I_{CC} V_{CC}$ , and the no load dynamic current consumption,  $I_S = C_{PD} V_{CC} f + I_{CC}$ .


## MM74HC125, MM74HC126

### ORDERING INFORMATION

| Part Number   | Marking    | Package                                          | Shipping <sup>†</sup> |
|---------------|------------|--------------------------------------------------|-----------------------|
| MM74HC125M    | HC125A     | SOIC-14, Case 751A<br>(Pb-Free, Halide Free)     | 55 Units / Tube       |
| MM74HC125MX   | HC125A     | SOIC-14, Case 751A<br>(Pb-Free, Halide Free)     | 2500 / Tape & Reel    |
| MM74HC125MTC  | HC<br>125A | TSSOP-14, Case 948G<br>(Pb-Free, Halide Free)    | 96 Units / Tube       |
| MM74HC125MTCX | HC<br>125A | TSSOP-14 WB, Case 948G<br>(Pb-Free, Halide Free) | 2500 / Tape & Reel    |
| MM74HC126M    | HC126A     | SOIC-14, Case 751A<br>(Pb-Free, Halide Free)     | 55 Units / Tube       |
| MM74HC126MX   | HC126A     | SOIC-14, Case 751EF<br>(Pb-Free, Halide Free)    | 2500 / Tape & Reel    |
| MM74HC126MTCX | HC<br>126A | TSSOP-14 WB, Case 948G<br>(Pb-Free, Halide Free) | 2500 / Tape & Reel    |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.




NOTE: Device also available in Tape and Reel. Specify by appending suffix letter "X" to the ordering number.



SCALE 1:1


**SOIC-14 NB**  
**CASE 751A-03**  
**ISSUE L**

DATE 03 FEB 2016


**NOTES:**


1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION b DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE PROTRUSION SHALL BE 0.13 TOTAL IN EXCESS OF AT MAXIMUM MATERIAL CONDITION.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD PROTRUSIONS.
5. MAXIMUM MOLD PROTRUSION 0.15 PER SIDE.

| DIM | MILLIMETERS |      | INCHES    |       |
|-----|-------------|------|-----------|-------|
|     | MIN         | MAX  | MIN       | MAX   |
| A   | 1.35        | 1.75 | 0.054     | 0.068 |
| A1  | 0.10        | 0.25 | 0.004     | 0.010 |
| A3  | 0.19        | 0.25 | 0.008     | 0.010 |
| b   | 0.35        | 0.49 | 0.014     | 0.019 |
| D   | 8.55        | 8.75 | 0.337     | 0.344 |
| E   | 3.80        | 4.00 | 0.150     | 0.157 |
| e   | 1.27 BSC    |      | 0.050 BSC |       |
| H   | 5.80        | 6.20 | 0.228     | 0.244 |
| h   | 0.25        | 0.50 | 0.010     | 0.019 |
| L   | 0.40        | 1.25 | 0.016     | 0.049 |
| M   | 0°          | 7°   | 0°        | 7°    |

**SOLDERING FOOTPRINT\***


DIMENSIONS: MILLIMETERS

\*For additional information on our Pb-Free strategy and soldering details, please download the **onsemi** Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

**GENERIC MARKING DIAGRAM\***


XXXXXX = Specific Device Code  
A = Assembly Location  
WL = Wafer Lot  
Y = Year  
WW = Work Week  
G = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

**STYLES ON PAGE 2**

|                         |                    |                                                                                                                                                                                     |
|-------------------------|--------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98ASB42565B</b> | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>SOIC-14 NB</b>  | <b>PAGE 1 OF 2</b>                                                                                                                                                                  |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**SOIC-14**  
**CASE 751A-03**  
**ISSUE L**

DATE 03 FEB 2016

STYLE 1:  
 PIN 1. COMMON CATHODE  
 2. ANODE/CATHODE  
 3. ANODE/CATHODE  
 4. NO CONNECTION  
 5. ANODE/CATHODE  
 6. NO CONNECTION  
 7. ANODE/CATHODE  
 8. ANODE/CATHODE  
 9. ANODE/CATHODE  
 10. NO CONNECTION  
 11. ANODE/CATHODE  
 12. ANODE/CATHODE  
 13. NO CONNECTION  
 14. COMMON ANODE

STYLE 2:  
 CANCELLED

STYLE 3:  
 PIN 1. NO CONNECTION  
 2. ANODE  
 3. ANODE  
 4. NO CONNECTION  
 5. ANODE  
 6. NO CONNECTION  
 7. ANODE  
 8. ANODE  
 9. ANODE  
 10. NO CONNECTION  
 11. ANODE  
 12. ANODE  
 13. NO CONNECTION  
 14. COMMON CATHODE

STYLE 4:  
 PIN 1. NO CONNECTION  
 2. CATHODE  
 3. CATHODE  
 4. NO CONNECTION  
 5. CATHODE  
 6. NO CONNECTION  
 7. CATHODE  
 8. CATHODE  
 9. CATHODE  
 10. NO CONNECTION  
 11. CATHODE  
 12. CATHODE  
 13. NO CONNECTION  
 14. COMMON ANODE

STYLE 5:  
 PIN 1. COMMON CATHODE  
 2. ANODE/CATHODE  
 3. ANODE/CATHODE  
 4. ANODE/CATHODE  
 5. ANODE/CATHODE  
 6. NO CONNECTION  
 7. COMMON ANODE  
 8. COMMON CATHODE  
 9. ANODE/CATHODE  
 10. ANODE/CATHODE  
 11. ANODE/CATHODE  
 12. ANODE/CATHODE  
 13. NO CONNECTION  
 14. COMMON ANODE

STYLE 6:  
 PIN 1. CATHODE  
 2. CATHODE  
 3. CATHODE  
 4. CATHODE  
 5. CATHODE  
 6. CATHODE  
 7. CATHODE  
 8. ANODE  
 9. ANODE  
 10. ANODE  
 11. ANODE  
 12. ANODE  
 13. ANODE  
 14. ANODE

STYLE 7:  
 PIN 1. ANODE/CATHODE  
 2. COMMON ANODE  
 3. COMMON CATHODE  
 4. ANODE/CATHODE  
 5. ANODE/CATHODE  
 6. ANODE/CATHODE  
 7. ANODE/CATHODE  
 8. ANODE/CATHODE  
 9. ANODE/CATHODE  
 10. ANODE/CATHODE  
 11. COMMON CATHODE  
 12. COMMON ANODE  
 13. ANODE/CATHODE  
 14. ANODE/CATHODE


STYLE 8:  
 PIN 1. COMMON CATHODE  
 2. ANODE/CATHODE  
 3. ANODE/CATHODE  
 4. NO CONNECTION  
 5. ANODE/CATHODE  
 6. ANODE/CATHODE  
 7. COMMON ANODE  
 8. COMMON ANODE  
 9. ANODE/CATHODE  
 10. ANODE/CATHODE  
 11. NO CONNECTION  
 12. ANODE/CATHODE  
 13. ANODE/CATHODE  
 14. COMMON CATHODE

|                         |                    |                                                                                                                                                                                     |
|-------------------------|--------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98ASB42565B</b> | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>SOIC-14 NB</b>  | <b>PAGE 2 OF 2</b>                                                                                                                                                                  |

**onsemi** and **onsemi** are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.


**SOIC14**  
**CASE 751EF**  
**ISSUE O**

DATE 30 SEP 2016




**NOTES:**

- A. CONFORMS TO JEDEC MS-012, VARIATION AB, ISSUE C
- B. ALL DIMENSIONS ARE IN MILLIMETERS
- C. DIMENSIONS DO NOT INCLUDE MOLD FLASH OR BURRS
- D. LAND PATTERN STANDARD: SOIC127P600X145-14M
- E. CONFORMS TO ASME Y14.5M, 2009








|                         |                    |                                                                                                                                                                                     |
|-------------------------|--------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98AON13739G</b> | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>SOIC14</b>      | <b>PAGE 1 OF 1</b>                                                                                                                                                                  |

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.




TSSOP-14 5.00x4.40x0.95, 0.65P  
CASE 948G  
ISSUE D

DATE 30 JUN 2026




| MILLIMETERS               |          |      |      |
|---------------------------|----------|------|------|
| DIM                       | MIN      | NOM  | MAX  |
| A                         | ---      | ---  | 1.20 |
| A1                        | 0.05     | 0.10 | 0.15 |
| A2                        | 0.85     | 0.95 | 1.05 |
| b                         | 0.19     | 0.25 | 0.30 |
| b1                        | 0.19     | 0.22 | 0.25 |
| c                         | 0.09     | 0.15 | 0.20 |
| c1                        | 0.09     | 0.12 | 0.16 |
| D                         | 5.00 BSC |      |      |
| E                         | 6.40 BSC |      |      |
| E1                        | 4.40 BSC |      |      |
| e                         | 0.65 BSC |      |      |
| L                         | 0.50     | 0.63 | 0.75 |
| L1                        | 1.00 REF |      |      |
| L2                        | 0.25 BSC |      |      |
| ø                         | 0*       | 4*   | 8*   |
| TOLERANCE FORM & POSITION |          |      |      |
| aaa                       | 0.10     |      |      |
| bbb                       | 0.15     |      |      |
| ccc                       | 0.08     |      |      |
| ddd                       | 0.10     |      |      |
| eee                       | 0.10     |      |      |



RECOMMENDED MOUNTING FOOTPRINT

\*For additional information on our Pb-Free strategy and soldering details, please download the onsemi Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

GENERIC MARKING DIAGRAM\*



- NOTES:
1. DIMENSIONING AND TOLERANCING AS PER ASME Y14.5M, 2018.
  2. CONTROLLING DIMENSION: MILLIMETER.
  3. DIMENSION D DOES NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS. MOLD FLASH OR GATE BURRS SHALL NOT EXCEED 0.15 PER SIDE.
  4. DIMENSION E1 DOES NOT INCLUDE INTERLEAD FLASH OR PROTRUSION. INTERLEAD FLASH OR PROTRUSION SHALL NOT EXCEED 0.25 PER SIDE.
  5. DIMENSION b DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.08 TOTAL IN EXCESS OF THE b DIMENSION AT MAXIMUM MATERIAL CONDITION.
  6. TERMINAL NUMBERS ARE SHOWN FOR REFERENCE ONLY.

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

A = Assembly Location  
L = Wafer Lot  
Y = Year  
W = Work Week  
▪ = Pb-Free Package  
(Note: Microdot may be in either location)

|                  |                                |                                                                                                                                                                                  |
|------------------|--------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98ASH70246A                    | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | TSSOP-14 5.00x4.40x0.95, 0.65P | PAGE 1 OF 1                                                                                                                                                                      |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)

