

## MOTOR PLATFORM TEMPERATURE SENSOR

- Shrink Tube Encapsulation
- Fluoroplastics Insulated Wire
- Wide Temperature Design

### Product Description

The temperature sensor is designed to monitor the temperature of the electric motor system. The design combines a high precision and high sensitivity NTC thermistor, which is sealed and protected by fluoroplastics material. The design provides a rectangular or cylinder shape and smaller size, making the assembly well suited to motor stator system, industrial system or other temperature monitoring system. The sensor design to fulfill reliability requirements, including high and low temperature storage, temperature cycling testing, temperature/humidity cycling and ATF(Automatic Transmission Fluid) oil proof testing.

### Features

- NTC
- Temperature range: -40°C ~+200°C
- Insulation resistance:  $\geq 100\text{Mohm}$
- Dielectric strength: 3000VAC
- Rectangular or cylinder sensor body
- ATF oil proof

### Applications

- Motors
- Generators
- BESS(Battery Energy Storage System)
- BMS(Battery Management System)
- ECC(Electrical Control Cabinet)
- Air conditioning systems
- White Goods


## Sensor specifications

|                         |   |
|-------------------------|---|
| Sensor Dimension        | Rectangular: 3.4*1.9*19.5 mm                    |
|                         | Cylinder: 3.3*2.5*19.5 mm                       |
| Resistance Accuracy     | Option1: 0.913K $\Omega$ $\pm$ 1%@100°C         |
|                         | Option2: 1.196K $\Omega$ $\pm$ 3%@150°C         |
| Tolerance on Beta Value | Option1 B25/100: 3550 $\pm$ 0.8%                |
|                         | Option2 B25/85: 4390 $\pm$ 2%                   |
| Temperature Range       | -40°C~+200°C                                    |
| Response Time           | T63.2(25/85)<7s(Liquid)                         |
| Insulation Resistance   | $\geq$ 100M $\Omega$ @1000VDC, Room temperature |
| Dielectric Strength     | 3000VAC, 1mA Max, Room temperature              |


## Reliability

| Item                          | Condition   | Criteria   |
|-------------------------------|---|--|
| Thermal Cycling               | -55°C to +125°C, 1000cycles   | $\Delta R/R \leq \pm 3\%$<br>$\Delta B/B \leq \pm 3\%$ |
| Thermal Shock                 | -40°C to +150°C, 100cycles  | $\Delta R/R \leq \pm 3\%$<br>$\Delta B/B \leq \pm 3\%$ |
| Temperature and Humidity Test | 85RH/85°C 1000H   | $\Delta R/R \leq \pm 3\%$<br>$\Delta B/B \leq \pm 3\%$ |
| High Temperature Storage      | 200°C 1000H   | $\Delta R/R \leq \pm 3\%$<br>$\Delta B/B \leq \pm 3\%$ |
| Low Temperature Storage       | -40°C 1000H   | $\Delta R/R \leq \pm 3\%$<br>$\Delta B/B \leq \pm 3\%$ |
| Water Immersion               | 85°C 1000H  | $\Delta R/R \leq \pm 3\%$<br>$\Delta B/B \leq \pm 3\%$ |
| ATF Oil Proof                 | -40°C 500H & +150°C 500H  | $\Delta R/R \leq \pm 3\%$<br>$\Delta B/B \leq \pm 3\%$ |
| Insulating Paint Resistant    | 145°C $\pm$ 5°C, 6H   | $\Delta R/R \leq \pm 3\%$<br>$\Delta B/B \leq \pm 3\%$ |
| Mechincal Shock               | Half-sine. Peak value : 100g's ;<br>Duartion : 6ms ; velocity12.3ft/s | $\Delta R/R \leq \pm 3\%$<br>$\Delta B/B \leq \pm 3\%$ |
| Vibration Test                | 5g's for 20min<br>12cycles of 3 orientations<br>test from 10HZ~2000HZ | $\Delta R/R \leq \pm 3\%$<br>$\Delta B/B \leq \pm 3\%$ |

## Circuit Suggestion



**Diagrams and Dimensions**



**Ordering Information**

| Total Length                                    | Wire color   | Wire size option |
|---|--------------|------------------|
| Define 'L' Length in mm( Example: 550 = 550 mm) | Transparency | 22AWG or 26AWG   |

| Description  | Length | Wire size | Stocked Part Number |
|--|--------|-----------|---------------------|
| NTC Rectangular temperature sensor / R0.913KΩ±1%@100°C | 550    | 22AWG     | 20031343-00         |
| NTC Cylinder temperature sensor / R0.913KΩ±1%@100°C    | 550    | 22AWG     | 20031343-01         |
| NTC Rectangular temperature sensor / R1.196KΩ±3%@150°C | 550    | 22AWG     | 20029369-00         |
| NTC Cylinder temperature sensor / R1.196KΩ±3%@150°C    | 550    | 22AWG     | 20029369-01         |

**Recommended Storage Conditions**

The recommended storage conditions.

| Parameter                 | Symbol             | Min | Typical | Max | Units |
|---------------------------|--------------------|-----|---------|-----|-------|
| Storage Temperature Range | T <sub>store</sub> | -20 | +25     | +85 | °C    |

**Installation Tips**

- For the sensor assembly to accurately track temperature, it should be installed into a hole or holder to let the sensor head as close as measurement point.
- Don't grip the sensor head with high pressure.

**Compliance**

- RoHS and REACH Compliance

# MOTOR PLATFORM TEMPERATURE SENSOR

## R-T table

| Option1 :R100=0.913KΩ±1% B25/100=3550±0.8% |          |         |          |           |          |         |         |
|--|----------|---------|----------|-----------|----------|---------|---------|
| Temp.(°C)                                  | Mini(KΩ) | Nom(KΩ) | Max (KΩ) | Temp.(°C) | Min (KΩ) | Nom(KΩ) | Max(KΩ) |
| -40  | 201.286  | 212.379 | 224.061  | -2        | 28.995   | 30.119  | 31.283  |
| -39  | 189.785  | 200.149 | 211.058  | -1        | 27.751   | 28.816  | 29.919  |
| -38  | 179.027  | 188.715 | 198.908  | 0         | 26.568   | 27.578  | 28.624  |
| -37  | 168.962  | 178.022 | 187.549  | 1         | 25.445   | 26.403  | 27.395  |
| -36  | 159.538  | 168.015 | 176.924  | 2         | 24.376   | 25.285  | 26.226  |
| -35  | 150.710  | 158.645 | 166.982  | 3         | 23.358   | 24.221  | 25.113  |
| -34  | 142.438  | 149.869 | 157.672  | 4         | 22.388   | 23.207  | 24.054  |
| -33  | 134.681  | 141.643 | 148.951  | 5         | 21.464   | 22.242  | 23.045  |
| -32  | 127.404  | 133.930 | 140.777  | 6         | 20.583   | 21.322  | 22.085  |
| -31  | 120.574  | 126.695 | 133.112  | 7         | 19.744   | 20.445  | 21.170  |
| -30  | 114.161  | 119.903 | 125.921  | 8         | 18.943   | 19.609  | 20.297  |
| -29  | 108.137  | 113.526 | 119.172  | 9         | 18.179   | 18.812  | 19.466  |
| -28  | 102.474  | 107.534 | 112.833  | 10        | 17.450   | 18.052  | 18.673  |
| -27  | 97.149   | 101.903 | 106.878  | 11        | 16.754   | 17.327  | 17.917  |
| -26  | 92.140   | 96.607  | 101.281  | 12        | 16.090   | 16.634  | 17.195  |
| -25  | 87.426   | 91.626  | 96.017   | 13        | 15.456   | 15.974  | 16.507  |
| -24  | 82.987   | 86.937  | 91.065   | 14        | 14.850   | 15.343  | 15.850  |
| -23  | 78.805   | 82.521  | 86.405   | 15        | 14.272   | 14.740  | 15.222  |
| -22  | 74.864   | 78.362  | 82.016   | 16        | 13.718   | 14.164  | 14.623  |
| -21  | 71.148   | 74.442  | 77.881   | 17        | 13.190   | 13.614  | 14.051  |
| -20  | 67.643   | 70.746  | 73.984   | 18        | 12.684   | 13.088  | 13.504  |
| -19  | 64.336   | 67.260  | 70.310   | 19        | 12.201   | 12.586  | 12.981  |
| -18  | 61.214   | 63.971  | 66.845   | 20        | 11.739   | 12.105  | 12.481  |
| -17  | 58.266   | 60.865  | 63.574   | 21        | 11.296   | 11.645  | 12.004  |
| -16  | 55.480   | 57.932  | 60.487   | 22        | 10.873   | 11.205  | 11.547  |
| -15  | 52.847   | 55.161  | 57.571   | 23        | 10.468   | 10.784  | 11.109  |
| -14  | 50.357   | 52.542  | 54.816   | 24        | 10.080   | 10.381  | 10.691  |
| -13  | 48.002   | 50.066  | 52.212   | 25        | 9.708    | 9.996   | 10.291  |
| -12  | 45.774   | 47.723  | 49.750   | 26        | 9.352    | 9.626   | 9.907   |
| -11  | 43.664   | 45.506  | 47.421   | 27        | 9.011    | 9.272   | 9.540   |
| -10  | 41.666   | 43.408  | 45.217   | 28        | 8.684    | 8.933   | 9.189   |
| -9   | 39.774   | 41.420  | 43.131   | 29        | 8.371    | 8.608   | 8.852   |
| -8   | 37.980   | 39.537  | 41.155   | 30        | 8.070    | 8.297   | 8.529   |
| -7   | 36.279   | 37.753  | 39.283   | 31        | 7.782    | 7.998   | 8.220   |
| -6   | 34.666   | 36.061  | 37.509   | 32        | 7.506    | 7.712   | 7.923   |
| -5   | 33.136   | 34.457  | 35.827   | 33        | 7.241    | 7.437   | 7.639   |
| -4   | 31.684   | 32.935  | 34.232   | 34        | 6.986    | 7.174   | 7.366   |
| -3   | 30.305   | 31.490  | 32.719   | 35        | 6.742    | 6.921   | 7.105   |

## MOTOR PLATFORM TEMPERATURE SENSOR

| Option1 :R100=0.913KΩ±1% B25/100=3550±0.8% |          |         |          |           |          |         |         |
|--|----------|---------|----------|-----------|----------|---------|---------|
| Temp.(°C)                                  | Mini(KΩ) | Nom(KΩ) | Max (KΩ) | Temp.(°C) | Min (KΩ) | Nom(KΩ) | Max(KΩ) |
| 36   | 6.507    | 6.679   | 6.854    | 78        | 1.694    | 1.720   | 1.746   |
| 37   | 6.282    | 6.446   | 6.613    | 79        | 1.644    | 1.669   | 1.693   |
| 38   | 6.066    | 6.222   | 6.382    | 80        | 1.596    | 1.619   | 1.643   |
| 39   | 5.858    | 6.008   | 6.160    | 81        | 1.549    | 1.572   | 1.594   |
| 40   | 5.659    | 5.801   | 5.947    | 82        | 1.504    | 1.526   | 1.547   |
| 41   | 5.467    | 5.603   | 5.742    | 83        | 1.461    | 1.481   | 1.502   |
| 42   | 5.283    | 5.413   | 5.545    | 84        | 1.419    | 1.438   | 1.458   |
| 43   | 5.106    | 5.230   | 5.356    | 85        | 1.378    | 1.396   | 1.415   |
| 44   | 4.935    | 5.054   | 5.175    | 86        | 1.338    | 1.356   | 1.374   |
| 45   | 4.771    | 4.885   | 5.000    | 87        | 1.300    | 1.317   | 1.335   |
| 46   | 4.614    | 4.722   | 4.832    | 88        | 1.264    | 1.280   | 1.296   |
| 47   | 4.462    | 4.566   | 4.671    | 89        | 1.228    | 1.243   | 1.259   |
| 48   | 4.316    | 4.415   | 4.516    | 90        | 1.194    | 1.208   | 1.223   |
| 49   | 4.176    | 4.270   | 4.367    | 91        | 1.160    | 1.174   | 1.188   |
| 50   | 4.041    | 4.131   | 4.223    | 92        | 1.128    | 1.141   | 1.155   |
| 51   | 3.910    | 3.997   | 4.085    | 93        | 1.097    | 1.109   | 1.122   |
| 52   | 3.785    | 3.868   | 3.952    | 94        | 1.066    | 1.079   | 1.091   |
| 53   | 3.664    | 3.743   | 3.824    | 95        | 1.037    | 1.049   | 1.060   |
| 54   | 3.548    | 3.623   | 3.700    | 96        | 1.009    | 1.020   | 1.031   |
| 55   | 3.436    | 3.508   | 3.581    | 97        | 0.981    | 0.992   | 1.002   |
| 56   | 3.328    | 3.397   | 3.467    | 98        | 0.955    | 0.965   | 0.975   |
| 57   | 3.224    | 3.290   | 3.357    | 99        | 0.929    | 0.938   | 0.948   |
| 58   | 3.123    | 3.186   | 3.251    | 100       | 0.904    | 0.913   | 0.922   |
| 59   | 3.026    | 3.087   | 3.148    | 101       | 0.879    | 0.888   | 0.897   |
| 60   | 2.933    | 2.991   | 3.050    | 102       | 0.855    | 0.864   | 0.873   |
| 61   | 2.843    | 2.898   | 2.955    | 103       | 0.832    | 0.841   | 0.850   |
| 62   | 2.756    | 2.809   | 2.863    | 104       | 0.809    | 0.818   | 0.827   |
| 63   | 2.672    | 2.723   | 2.775    | 105       | 0.788    | 0.797   | 0.805   |
| 64   | 2.592    | 2.640   | 2.689    | 106       | 0.767    | 0.775   | 0.784   |
| 65   | 2.514    | 2.560   | 2.607    | 107       | 0.746    | 0.755   | 0.764   |
| 66   | 2.438    | 2.483   | 2.528    | 108       | 0.726    | 0.735   | 0.744   |
| 67   | 2.366    | 2.408   | 2.451    | 109       | 0.707    | 0.716   | 0.724   |
| 68   | 2.295    | 2.336   | 2.377    | 110       | 0.689    | 0.697   | 0.706   |
| 69   | 2.227    | 2.266   | 2.306    | 111       | 0.671    | 0.679   | 0.688   |
| 70   | 2.162    | 2.199   | 2.237    | 112       | 0.653    | 0.662   | 0.670   |
| 71   | 2.096    | 2.132   | 2.167    | 113       | 0.636    | 0.645   | 0.653   |
| 72   | 2.032    | 2.066   | 2.101    | 114       | 0.620    | 0.628   | 0.636   |
| 73   | 1.971    | 2.003   | 2.036    | 115       | 0.604    | 0.612   | 0.620   |
| 74   | 1.911    | 1.942   | 1.974    | 116       | 0.589    | 0.597   | 0.605   |
| 75   | 1.854    | 1.884   | 1.914    | 117       | 0.574    | 0.582   | 0.590   |
| 76   | 1.799    | 1.827   | 1.856    | 118       | 0.559    | 0.567   | 0.575   |
| 77   | 1.745    | 1.772   | 1.800    | 119       | 0.545    | 0.553   | 0.561   |

## MOTOR PLATFORM TEMPERATURE SENSOR

| Option1 :R100=0.913KΩ±1% B25/100=3550±0.8% |          |         |          |           |          |         |         |
|--|----------|---------|----------|-----------|----------|---------|---------|
| Temp.(°C)                                  | Mini(KΩ) | Nom(KΩ) | Max (KΩ) | Temp.(°C) | Min (KΩ) | Nom(KΩ) | Max(KΩ) |
| 120  | 0.532    | 0.539   | 0.547    | 161       | 0.207    | 0.211   | 0.216   |
| 121  | 0.518    | 0.526   | 0.534    | 162       | 0.202    | 0.207   | 0.211   |
| 122  | 0.506    | 0.513   | 0.521    | 163       | 0.198    | 0.202   | 0.207   |
| 123  | 0.493    | 0.500   | 0.508    | 164       | 0.194    | 0.198   | 0.203   |
| 124  | 0.481    | 0.488   | 0.496    | 165       | 0.190    | 0.194   | 0.199   |
| 125  | 0.469    | 0.476   | 0.484    | 166       | 0.186    | 0.190   | 0.195   |
| 126  | 0.458    | 0.465   | 0.472    | 167       | 0.182    | 0.187   | 0.191   |
| 127  | 0.447    | 0.454   | 0.461    | 168       | 0.179    | 0.183   | 0.187   |
| 128  | 0.436    | 0.443   | 0.450    | 169       | 0.175    | 0.179   | 0.183   |
| 129  | 0.425    | 0.432   | 0.439    | 170       | 0.171    | 0.176   | 0.180   |
| 130  | 0.415    | 0.422   | 0.429    | 171       | 0.168    | 0.172   | 0.176   |
| 131  | 0.405    | 0.412   | 0.419    | 172       | 0.165    | 0.169   | 0.173   |
| 132  | 0.396    | 0.402   | 0.409    | 173       | 0.161    | 0.165   | 0.169   |
| 133  | 0.386    | 0.393   | 0.400    | 174       | 0.158    | 0.162   | 0.166   |
| 134  | 0.377    | 0.384   | 0.390    | 175       | 0.155    | 0.159   | 0.163   |
| 135  | 0.369    | 0.375   | 0.381    | 176       | 0.152    | 0.156   | 0.160   |
| 136  | 0.360    | 0.366   | 0.373    | 177       | 0.149    | 0.153   | 0.156   |
| 137  | 0.352    | 0.358   | 0.364    | 178       | 0.146    | 0.150   | 0.153   |
| 138  | 0.343    | 0.350   | 0.356    | 179       | 0.143    | 0.147   | 0.151   |
| 139  | 0.336    | 0.342   | 0.348    | 180       | 0.141    | 0.144   | 0.148   |
| 140  | 0.328    | 0.334   | 0.340    | 181       | 0.138    | 0.141   | 0.145   |
| 141  | 0.320    | 0.326   | 0.332    | 182       | 0.135    | 0.139   | 0.142   |
| 142  | 0.313    | 0.319   | 0.325    | 183       | 0.133    | 0.136   | 0.139   |
| 143  | 0.306    | 0.312   | 0.318    | 184       | 0.130    | 0.133   | 0.137   |
| 144  | 0.299    | 0.305   | 0.311    | 185       | 0.128    | 0.131   | 0.134   |
| 145  | 0.293    | 0.298   | 0.304    | 186       | 0.125    | 0.128   | 0.132   |
| 146  | 0.286    | 0.292   | 0.297    | 187       | 0.123    | 0.126   | 0.129   |
| 147  | 0.280    | 0.285   | 0.291    | 188       | 0.121    | 0.124   | 0.127   |
| 148  | 0.274    | 0.279   | 0.284    | 189       | 0.118    | 0.121   | 0.125   |
| 149  | 0.267    | 0.273   | 0.278    | 190       | 0.116    | 0.119   | 0.122   |
| 150  | 0.262    | 0.267   | 0.272    | 191       | 0.114    | 0.117   | 0.120   |
| 151  | 0.256    | 0.261   | 0.266    | 192       | 0.112    | 0.115   | 0.118   |
| 152  | 0.250    | 0.256   | 0.261    | 193       | 0.110    | 0.113   | 0.116   |
| 153  | 0.245    | 0.250   | 0.255    | 194       | 0.108    | 0.111   | 0.114   |
| 154  | 0.240    | 0.245   | 0.250    | 195       | 0.106    | 0.109   | 0.112   |
| 155  | 0.235    | 0.240   | 0.245    | 196       | 0.104    | 0.107   | 0.110   |
| 156  | 0.230    | 0.235   | 0.239    | 197       | 0.102    | 0.105   | 0.108   |
| 157  | 0.225    | 0.230   | 0.234    | 198       | 0.100    | 0.103   | 0.106   |
| 158  | 0.220    | 0.225   | 0.230    | 199       | 0.098    | 0.101   | 0.104   |
| 159  | 0.215    | 0.220   | 0.225    | 200       | 0.096    | 0.099   | 0.102   |
| 160  | 0.211    | 0.216   | 0.220    |           |          |         |         |

R-T table

| Option2 :R150=1.196KΩ±3% B25/85=4390±2% |          |          |          |           |          |         |         |
|---|----------|----------|----------|-----------|----------|---------|---------|
| Temp.(°C)                               | Mini(KΩ) | Nom(KΩ)  | Max (KΩ) | Temp.(°C) | Min (KΩ) | Nom(KΩ) | Max(KΩ) |
| -40                                     | 3859.095 | 4694.517 | 5705.652 | -2        | 344.537  | 398.959 | 461.562 |
| -39                                     | 3585.735 | 4355.444 | 5285.617 | -1        | 325.860  | 376.903 | 435.549 |
| -38                                     | 3334.254 | 4043.976 | 4900.353 | 0         | 308.299  | 356.188 | 411.145 |
| -37                                     | 3102.661 | 3757.561 | 4546.601 | 1         | 291.781  | 336.726 | 388.244 |
| -36                                     | 2889.167 | 3493.917 | 4221.448 | 2         | 276.240  | 318.434 | 366.744 |
| -35                                     | 2692.174 | 3251.001 | 3922.294 | 3         | 261.612  | 301.238 | 346.554 |
| -34                                     | 2510.238 | 3026.975 | 3646.797 | 4         | 247.841  | 285.066 | 327.587 |
| -33                                     | 2342.061 | 2820.183 | 3392.857 | 5         | 234.871  | 269.852 | 309.764 |
| -32                                     | 2186.471 | 2629.139 | 3158.584 | 6         | 222.653  | 255.535 | 293.010 |
| -31                                     | 2042.407 | 2452.495 | 2942.272 | 7         | 211.139  | 242.059 | 277.257 |
| -30                                     | 1908.913 | 2289.037 | 2742.386 | 8         | 200.286  | 229.369 | 262.438 |
| -29                                     | 1785.121 | 2137.667 | 2557.534 | 9         | 190.052  | 217.416 | 248.496 |
| -28                                     | 1670.242 | 1997.387 | 2386.459 | 10        | 180.399  | 206.154 | 235.374 |
| -27                                     | 1563.559 | 1867.292 | 2228.020 | 11        | 171.292  | 195.540 | 223.019 |
| -26                                     | 1464.424 | 1746.563 | 2081.184 | 12        | 162.697  | 185.533 | 211.384 |
| -25                                     | 1372.242 | 1634.450 | 1945.009 | 13        | 154.583  | 176.096 | 200.423 |
| -24                                     | 1286.471 | 1530.273 | 1818.641 | 14        | 146.921  | 167.195 | 190.094 |
| -23                                     | 1206.619 | 1433.412 | 1701.301 | 15        | 139.684  | 158.795 | 180.358 |
| -22                                     | 1132.234 | 1343.301 | 1592.279 | 16        | 132.846  | 150.867 | 171.178 |
| -21                                     | 1062.902 | 1259.419 | 1490.926 | 17        | 126.383  | 143.381 | 162.519 |
| -20                                     | 998.245  | 1181.294 | 1396.650 | 18        | 120.273  | 136.312 | 154.350 |
| -19                                     | 937.917  | 1108.492 | 1308.910 | 19        | 114.495  | 129.633 | 146.640 |
| -18                                     | 881.599  | 1040.616 | 1227.210 | 20        | 109.030  | 123.322 | 139.362 |
| -17                                     | 828.999  | 977.301  | 1151.096 | 21        | 103.859  | 117.357 | 132.490 |
| -16                                     | 779.848  | 918.210  | 1080.149 | 22        | 98.965   | 111.717 | 125.998 |
| -15                                     | 733.897  | 863.037  | 1013.988 | 23        | 94.332   | 106.382 | 119.864 |
| -14                                     | 690.921  | 811.499  | 952.261  | 24        | 89.945   | 101.336 | 114.067 |
| -13                                     | 650.708  | 763.333  | 894.645  | 25        | 85.789   | 96.561  | 108.587 |
| -12                                     | 613.064  | 718.300  | 840.842  | 26        | 81.815   | 91.999  | 103.357 |
| -11                                     | 577.812  | 676.178  | 790.579  | 27        | 78.047   | 87.678  | 98.408  |
| -10                                     | 544.785  | 636.764  | 743.602  | 28        | 74.474   | 83.583  | 93.723  |
| -9                                      | 513.831  | 599.867  | 699.678  | 29        | 71.084   | 79.703  | 89.287  |
| -8                                      | 484.808  | 565.313  | 658.593  | 30        | 67.867   | 76.024  | 85.085  |
| -7                                      | 457.586  | 532.942  | 620.149  | 31        | 64.814   | 72.536  | 81.104  |
| -6                                      | 432.043  | 502.603  | 584.160  | 32        | 61.914   | 69.226  | 77.332  |
| -5                                      | 408.067  | 474.159  | 550.459  | 33        | 59.161   | 66.086  | 73.755  |
| -4                                      | 385.554  | 447.481  | 518.887  | 34        | 56.544   | 63.105  | 70.364  |
| -3                                      | 364.408  | 422.451  | 489.299  | 35        | 54.058   | 60.275  | 67.146  |

## MOTOR PLATFORM TEMPERATURE SENSOR

Option2 :R150=1.196K $\Omega$  $\pm$ 3% B25/85=4390 $\pm$ 2%

| Temp.(°C) | Mini(K $\Omega$ ) | Nom(K $\Omega$ ) | Max (K $\Omega$ ) | Temp.(°C) | Min (K $\Omega$ ) | Nom(K $\Omega$ ) | Max(K $\Omega$ ) |
|-----------|-------------------|------------------|-------------------|-----------|-------------------|------------------|------------------|
| 36        | 51.695            | 57.587           | 64.094            | 78        | 9.754             | 10.502           | 11.298           |
| 37        | 49.448            | 55.034           | 61.197            | 79        | 9.416             | 10.131           | 10.890           |
| 38        | 47.310            | 52.608           | 58.446            | 80        | 9.091             | 9.774            | 10.500           |
| 39        | 45.277            | 50.302           | 55.834            | 81        | 8.779             | 9.432            | 10.125           |
| 40        | 43.342            | 48.109           | 53.352            | 82        | 8.480             | 9.104            | 9.766            |
| 41        | 41.500            | 46.024           | 50.995            | 83        | 8.192             | 8.789            | 9.421            |
| 42        | 39.746            | 44.040           | 48.754            | 84        | 7.915             | 8.486            | 9.090            |
| 43        | 38.076            | 42.152           | 46.623            | 85        | 7.649             | 8.195            | 8.772            |
| 44        | 36.485            | 40.356           | 44.597            | 86        | 7.394             | 7.916            | 8.468            |
| 45        | 34.969            | 38.645           | 42.670            | 87        | 7.149             | 7.649            | 8.176            |
| 46        | 33.524            | 37.016           | 40.836            | 88        | 6.913             | 7.391            | 7.896            |
| 47        | 32.146            | 35.465           | 39.091            | 89        | 6.686             | 7.144            | 7.626            |
| 48        | 30.832            | 33.986           | 37.430            | 90        | 6.468             | 6.906            | 7.367            |
| 49        | 29.579            | 32.578           | 35.848            | 91        | 6.258             | 6.677            | 7.118            |
| 50        | 28.384            | 31.234           | 34.341            | 92        | 6.056             | 6.457            | 6.879            |
| 51        | 27.243            | 29.954           | 32.905            | 93        | 5.861             | 6.246            | 6.649            |
| 52        | 26.153            | 28.732           | 31.537            | 94        | 5.674             | 6.042            | 6.428            |
| 53        | 25.113            | 27.567           | 30.233            | 95        | 5.493             | 5.846            | 6.215            |
| 54        | 24.120            | 26.455           | 28.989            | 96        | 5.319             | 5.657            | 6.011            |
| 55        | 23.172            | 25.394           | 27.804            | 97        | 5.152             | 5.475            | 5.814            |
| 56        | 22.265            | 24.380           | 26.673            | 98        | 4.990             | 5.300            | 5.624            |
| 57        | 21.399            | 23.413           | 25.593            | 99        | 4.835             | 5.131            | 5.442            |
| 58        | 20.571            | 22.489           | 24.563            | 100       | 4.685             | 4.969            | 5.266            |
| 59        | 19.779            | 21.606           | 23.580            | 101       | 4.540             | 4.812            | 5.097            |
| 60        | 19.022            | 20.762           | 22.641            | 102       | 4.400             | 4.662            | 4.934            |
| 61        | 18.297            | 19.956           | 21.744            | 103       | 4.266             | 4.516            | 4.777            |
| 62        | 17.604            | 19.185           | 20.888            | 104       | 4.136             | 4.376            | 4.626            |
| 63        | 16.941            | 18.447           | 20.069            | 105       | 4.011             | 4.241            | 4.480            |
| 64        | 16.306            | 17.742           | 19.287            | 106       | 3.890             | 4.111            | 4.340            |
| 65        | 15.698            | 17.067           | 18.539            | 107       | 3.773             | 3.985            | 4.204            |
| 66        | 15.116            | 16.422           | 17.824            | 108       | 3.661             | 3.864            | 4.074            |
| 67        | 14.559            | 15.804           | 17.141            | 109       | 3.552             | 3.747            | 3.948            |
| 68        | 14.024            | 15.213           | 16.487            | 110       | 3.447             | 3.634            | 3.827            |
| 69        | 13.512            | 14.646           | 15.861            | 111       | 3.346             | 3.525            | 3.710            |
| 70        | 13.022            | 14.104           | 15.262            | 112       | 3.248             | 3.420            | 3.597            |
| 71        | 12.551            | 13.584           | 14.688            | 113       | 3.153             | 3.318            | 3.488            |
| 72        | 12.100            | 13.086           | 14.139            | 114       | 3.062             | 3.220            | 3.383            |
| 73        | 11.668            | 12.609           | 13.614            | 115       | 2.974             | 3.125            | 3.281            |
| 74        | 11.253            | 12.151           | 13.110            | 116       | 2.888             | 3.034            | 3.183            |
| 75        | 10.855            | 11.713           | 12.628            | 117       | 2.806             | 2.945            | 3.089            |
| 76        | 10.473            | 11.292           | 12.165            | 118       | 2.726             | 2.860            | 2.997            |
| 77        | 10.106            | 10.889           | 11.722            | 119       | 2.649             | 2.777            | 2.909            |

## MOTOR PLATFORM TEMPERATURE SENSOR

| Option2 :R150=1.196KΩ±3% B25/85=4390±2% |          |         |          |           |          |         |         |
|---|----------|---------|----------|-----------|----------|---------|---------|
| Temp.(°C)                               | Mini(KΩ) | Nom(KΩ) | Max (KΩ) | Temp.(°C) | Min (KΩ) | Nom(KΩ) | Max(KΩ) |
| 120                                     | 2.574    | 2.698   | 2.824    | 161       | 0.880    | 0.912   | 0.944   |
| 121                                     | 2.502    | 2.620   | 2.742    | 162       | 0.858    | 0.890   | 0.922   |
| 122                                     | 2.433    | 2.546   | 2.662    | 163       | 0.838    | 0.869   | 0.901   |
| 123                                     | 2.365    | 2.474   | 2.585    | 164       | 0.818    | 0.849   | 0.880   |
| 124                                     | 2.300    | 2.404   | 2.511    | 165       | 0.798    | 0.829   | 0.860   |
| 125                                     | 2.236    | 2.337   | 2.439    | 166       | 0.779    | 0.810   | 0.840   |
| 126                                     | 2.175    | 2.271   | 2.370    | 167       | 0.761    | 0.791   | 0.821   |
| 127                                     | 2.116    | 2.208   | 2.303    | 168       | 0.743    | 0.773   | 0.803   |
| 128                                     | 2.059    | 2.147   | 2.238    | 169       | 0.726    | 0.755   | 0.785   |
| 129                                     | 2.003    | 2.088   | 2.175    | 170       | 0.709    | 0.738   | 0.767   |
| 130                                     | 1.949    | 2.031   | 2.114    | 171       | 0.692    | 0.721   | 0.750   |
| 131                                     | 1.897    | 1.975   | 2.055    | 172       | 0.676    | 0.704   | 0.733   |
| 132                                     | 1.847    | 1.922   | 1.998    | 173       | 0.660    | 0.688   | 0.717   |
| 133                                     | 1.798    | 1.870   | 1.943    | 174       | 0.645    | 0.673   | 0.701   |
| 134                                     | 1.750    | 1.820   | 1.890    | 175       | 0.631    | 0.658   | 0.686   |
| 135                                     | 1.704    | 1.771   | 1.838    | 176       | 0.616    | 0.643   | 0.671   |
| 136                                     | 1.660    | 1.724   | 1.788    | 177       | 0.602    | 0.629   | 0.656   |
| 137                                     | 1.617    | 1.678   | 1.740    | 178       | 0.589    | 0.615   | 0.642   |
| 138                                     | 1.575    | 1.634   | 1.693    | 179       | 0.575    | 0.601   | 0.628   |
| 139                                     | 1.534    | 1.591   | 1.648    | 180       | 0.563    | 0.588   | 0.615   |
| 140                                     | 1.495    | 1.549   | 1.604    | 181       | 0.550    | 0.576   | 0.602   |
| 141                                     | 1.457    | 1.509   | 1.561    | 182       | 0.538    | 0.563   | 0.589   |
| 142                                     | 1.420    | 1.470   | 1.520    | 183       | 0.526    | 0.551   | 0.576   |
| 143                                     | 1.384    | 1.432   | 1.480    | 184       | 0.514    | 0.539   | 0.564   |
| 144                                     | 1.349    | 1.395   | 1.441    | 185       | 0.503    | 0.527   | 0.552   |
| 145                                     | 1.315    | 1.359   | 1.403    | 186       | 0.492    | 0.516   | 0.541   |
| 146                                     | 1.282    | 1.325   | 1.367    | 187       | 0.481    | 0.505   | 0.529   |
| 147                                     | 1.250    | 1.291   | 1.332    | 188       | 0.471    | 0.494   | 0.518   |
| 148                                     | 1.219    | 1.258   | 1.297    | 189       | 0.461    | 0.484   | 0.507   |
| 149                                     | 1.189    | 1.227   | 1.264    | 190       | 0.451    | 0.474   | 0.497   |
| 150                                     | 1.160    | 1.196   | 1.232    | 191       | 0.441    | 0.464   | 0.487   |
| 151                                     | 1.131    | 1.166   | 1.202    | 192       | 0.432    | 0.454   | 0.477   |
| 152                                     | 1.102    | 1.137   | 1.173    | 193       | 0.423    | 0.445   | 0.467   |
| 153                                     | 1.074    | 1.109   | 1.144    | 194       | 0.414    | 0.435   | 0.458   |
| 154                                     | 1.047    | 1.082   | 1.117    | 195       | 0.405    | 0.427   | 0.448   |
| 155                                     | 1.021    | 1.056   | 1.090    | 196       | 0.397    | 0.418   | 0.440   |
| 156                                     | 0.996    | 1.030   | 1.064    | 197       | 0.389    | 0.409   | 0.431   |
| 157                                     | 0.971    | 1.005   | 1.039    | 198       | 0.380    | 0.401   | 0.422   |
| 158                                     | 0.947    | 0.981   | 1.014    | 199       | 0.373    | 0.393   | 0.414   |
| 159                                     | 0.924    | 0.957   | 0.990    | 200       | 0.365    | 0.385   | 0.406   |
| 160                                     | 0.902    | 0.934   | 0.967    |           |          |         |         |

## Change History

| Date       | Version | Change Description |
|------------|---------|--------------------|
| 2024-08-30 | A       | Initial Release    |
|            |         |                    |

[CLICK HERE >](#)  
**CONNECT WITH A SPECIALIST**

**NORTH AMERICA**  
Tel +1 800 522 6752

**EUROPE**  
Tel +31 73 624 6999

**ASIA**  
Tel +86 0400 820 6015

[te.com/sensors](https://te.com/sensors)

TE Connectivity, TE, and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity Ltd. family of companies.

Apple, Google and Google Play are trademarks.

All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2024 TE Connectivity Corporation. All Rights Reserved

Published 01-2024

