


SECTION P-P



N = Number of poles  
Dim A=(N-1)X7.62+5.62  
Dim B=(N-1)x7.62  
Dim C=(N-1)x7.62+12.2  
Dim D=(N-1)x7.62+18.0

Poles	Tolerance	
	DIM A&B	DIM C&D
2p-6p	±0.15	±0.25
7p-12p	±0.20	±0.30
13p-16p	±0.30	±0.40

REV	DATE	ECN NO.	APPROVER
F	04/12-21	ECN202104004	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

## Material

- Item ① Clamp: Brass(CuZn) Ni plated
- Item ② Terminal screw: Steel Zinc plating "- " slot type
- Item ③ Female contact: PhBz ,Bright Tin plated over Nickel plated
- Item ④ Terminal Cover: Thermoplastic (UL94V-0)
- Item ⑤ Terminal housing: Thermoplastic (UL94V-0)
- Item ⑥ With flange screw: Steel Zinc plating M2.5"- " slot type

## Electrical cULus

- Voltage rating: 300VAC
- Current rating: 12A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 5Lb-In
- Screw: M3
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval:
- Critical dimension:

TJ xx 01 x 2 xxxx G

02 2 CONTACTS	0 Black (RAL9005)	G RoHS compliant (lead<4%) In copper Alloy
03 3 CONTACTS	2 Red (RAL3001/D)	
... ..	3 Orange(RAL2011/P)	
16 16 CONTACTS	4 Yellow(RAL1018/A)	
	5 Green(RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	
	9 White(RAL1102)	
	C Green(RAL6018/U)	
		0000 Standard @ Logo
		000A Standard ANY Logo
		Any special item by customer request, please contact sales department.

**Amphenol**  
**ANYTEK**

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TJ-7.62mm Series 2-16P with flange			
PART NO.	TJxx01x2xxxxG			DWG NO.	8TJ04.02
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Chen Bo 04/12-21	Chen Bo 04/12-21		
				UNIT: mm	X. ±0.50
				SCALE: NONE	X.X ±0.30
					X.XX ±0.10
					X° ±1°
SHEET: 01/01		REV.: F			