Honeywell

Honeywell Sensing and Control



Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

Keyword Search

Search for product and support information.

All Sensing and Contr


Product Search

Part number search:

Use (*) to expand search

Specification Search

101TL2834-3



Actual product appearance may vary.

TL Series Toggle Switch, 1 pole, 2 position, IWTS (16 -20 Gage) terminal, Standard Lever

Features

Environment-proof sealing
1,2, and 4 pole circuitry
Standard and pull-to-unlock levers
2 and 3 position, maintained and momentary toggle action
Temperature range:-85? F to +160? F
Completely sealed switching chamber
Step-design case provides added space between terminals to help prevent shorting
UL recognized, CSA certified
CE approved

Potential Applications


Industrial machinery and equipment
Military and commercial aviation
Construction equipment
Test instruments
Agricultural machinery
Process control
Medical instrumentation

Description

MICRO SWITCH™TL Series toggle switches have high strength, temperature resistant, non-tracking case material and silver cadmium oxide contacts. Pull-to-Unlock toggle levers prevent accidental operation; the lever must be pulled approx. 2,3 mm (0.09 inches) to change positions.

Supporting Documentation

- Accessory: Lever Sleeve
- Accessory: Seals
- Accessory: Nuts
- Engineering Drawing

Product Specifications	
Circuitry/Operating action	
Product Type	MICRO SWITCH™ Toggle Switch
Ampere/Voltage Range (Resistive Load)	0.01 A to 0.1 A at 0.5 Vdc to 28 Vdc,0.01 A to 0.1 A at 0.5 Vac to 115 Vac
Circuitry	SPDT
Action	2 position
Mounting	Bushing 15/32 in
Termination	IWTS (16 - 20 Gage)
Lever Type	Standard
Comment	Gold Plated Contacts
Availability	Global
UNSPSC Code	30211908
UNSPSC Commodity	30211908 Toggle switches
Series Name	TL

Downloaded from Arrow.com.