





Part Number : [511460400](#)
Product Description : 1.25mm Pitch
PanelMate Wire-to-Board Receptacle Housing,
Ultra Low Profile, 4 Circuits, Natural
Series Number : 51146
Status : New Business Not Supported
Product Category : Connector Housings



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
Category	Connector Housings
Series	51146
Description	1.25mm Pitch PanelMate Wire-to-Board Receptacle Housing, Ultra Low Profile, 4 Circuits, Natural
Application	Power, Wire-to-Board
Product Name	PanelMate
UPC	800754237451

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Net Weight	0.043/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Temperature Range - Operating	-40° to +85°C

This document was generated on Mar 06, 2025