molex



Part Number : 1202530074
Product Description : Contrinex Inductive Sensor, M30 Housing, 22mm Operating Distance, Quasi-embeddable, PNP, NO, 4-pin M12 Connector, 73.5mm Housing Length
Series Number : 120253
Status : Not Recommended For New Design
Product Category : Inductive and Photoelectric Sensors
Engineering Part Number : DW-AS-503-M30-002

Documents and Resources

Specifications

1202530068-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M30 Housing, 22mm Operating Distance, Quasi-embeddable, PNP, NO, 4-pin M12 Connector, 73.5mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130062447

Electrical

Output	NO
Polarity	PNP
Switching Frequency	≤ 200 Hz

Physical

Connection	Connector (M12, 4-pin)
Length	73.5mm
Material - Housing	Chrome Plated Brass
Material - Sensing Face	PBTP
Mounting Style	Quasi-embeddable

Downloaded from Arrow.com.

Operating Distance	22mm
Output	NO
Sensor Housing Size	M30
Temperature Range - Operating	-25° to +70°C

Downloaded from Arrow.com.