




6.6±0.2
FROM 12POS
TO 50POS
ONLY





- NOTES :
- 1 - MATERIAL : PA6.6 25% GLASSFILLED, UL-94V-0
 - 2 - FOR USE WITH MINITEK CTW CONTACTS:
AWG 26-30, SERIE 77138
AWG 22-24 SERIE 10044403
 - 3 - TO BE MATED WITH MINITEK HEADERS SERIES
98414 / 98416 / 98424 AND 10075025.
 - 4 - PRODUCT SPECIFICATIONS : GS12-415
 - 5 - PACKAGING BULK.
 - 6 - RoHS COMPLIANT, THE PRODUCT IS NOT
INTENDED TO BE EXPOSED TO ANY SOLDER
PROCESS.
 - 7 - THE TRIANGLE INDICATES THE FIRT POSITION
 - 8 - PRODUCT MEETS EUROPEAN UNION DIRTIVES
AND OTHERS COUNTRY REGULATIONS AS PER
GS-022-008.
 - 9 - FOR POLARIZATION, SPECIFIED CAVITY NUMBER
EXAMPLE : -B01 = ROW B, CAVITY 01 FILLED.
OMIT FROM PART NUMBER IF FEATURE NOT APPLICABLE.
 - 10- THIS PART SERIES IS NOT INITIALLY INTENDED FOR
AUTOMOTIVE APPLICATIONS. ADDITIONAL FEES ARE
CHARGEABLE FOR ANY ADDITIONAL QUALIFICATION AND
TEST REPORTS PERFORMED OUTSIDE THE SCOPE OF THE
STANDARD PRODUCT SPECIFICATIONS.
 - 11- UNLESS OTHERWISE APPROVED BY AMPHENOL, ALL PARTS
AND COMPONENTS ARE DESIGNED & BUILT ACCORDING TO
AMPHENOL'S SPECIFICATIONS WHICH ARE SUBJECT TO
CHANGE WITHOUT NOTICE.


EXTENDED RANGE

- TOOLING FEASIBILITY CONFIRMED
- SAMPLES ON DEMAND
- AVAILABILITY ON DEMAND

10073599-YXX-ZZZLF




CAVITY FILLED EXAMPLE
(...-B01LF)
SEE NOTE 9



LATCH DESIGN FOR 10073599-006LF
& 10073599-008LF ONLY

PART NUMBER	NBR OF POS	A+/-0.2	B
10073599-Y06LF	2x3	6.54	4
10073599-Y08LF	2x4	8.54	6
10073599-Y10LF	2x5	10.54	8
10073599-Y12LF	2x6	12.54	10
10073599-Y14LF	2x7	14.54	12
10073599-Y16LF	2x8	16.54	14
10073599-Y18LF	2x9	18.54	16
10073599-Y20LF	2x10	20.54	18
10073599-Y22LF	2x11	22.54	20
10073599-Y24LF	2x12	24.54	22
10073599-Y26LF	2x13	26.54	24
10073599-Y28LF	2x14	28.54	26
10073599-Y30LF	2x15	30.54	28
10073599-Y32LF	2x16	32.54	30
10073599-Y34LF	2x17	34.54	32
10073599-Y36LF	2x18	36.54	34
10073599-Y38LF	2x19	38.54	36
10073599-Y40LF	2x20	40.54	38
10073599-Y42LF	2x21	42.54	40
10073599-Y44LF	2x22	44.54	42
10073599-Y46LF	2x23	46.54	44
10073599-Y48LF	2x24	48.54	46
10073599-Y50LF	2x25	50.54	48



APPLICATION
SEE NOTE 2 & 3

spec ref		-		dr		Vernier, Benoi		2015/10/26		projection		mm		size		A3		scale		6:1	
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Laurent Mulin		2025/02/04						ecn no		ELX-F-54238-1					
chr				-		-															
appr				Lamy, Alexandr		2025/02/05		product family						rel level		Released					
surface		linear		0.X		±0.3		Amphenol FCI		title		MINITEK CTW		dwg no		10073599		rev		G	
				0.XX		±0.10															
				0.XXX		±0.05															
ISO 1302		angular		0°		±2°				cat. no.		Product - Customer Drw		sheet 1 of 1							