

Technical data sheet

Article number:
309-50643

TF24-6.4/3.2



Product Group	Heat shrinkable tubing 2:1 - flexible and transparent
Product Family	TF24
Material	Polyolefin, cross-linked (PO-X)
Colour	Transparent (CL)
Behaviour at Heat Shock	not dripping, not fluid, not cracking
Behaviour At Low Temperature	not cracking
Dielectric Strength	30 kV/mm
Elongation at break (min.)	450 %
Elongation At Heat Aging	250 %
Heat Aging Test	168h/175°C
Heat Shock Test	4h/250°C
Longitudinal Change After Shrinkage	+/-5% max.
Min. Shrink Temperature - °C	+110 °C
Operating Temperature	-55 °C to +135 °C
Package Content	60 m
Package Content packed in	reel
Recov. Ø d max.	3.2 mm
Shrink Ratio	2:1
Specifications	VG 95343-5:2016-10
Supplied Ø D min.	6.4 mm
Tensile Strength	20 MPa
Wall (WT)	0.64 mm
Water Absorption	0.2 %

