





PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)



ROHS PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	Gold Flash	0.76µ Gold	1.25µ Gold
09	30.81	24.99	16.96	16.79	10.96	D09P90C4GL00LF	D09P90C6GL00LF	D09P90C8GL00LF
15	39.14	33.32	25.18	25.12	19.18	D15P90C4GL00LF	D15P90C6GL00LF	D15P90C8GL00LF
25	53.03	47.04	39.12	38.84	33.12	D25P90C4GL00LF	D25P90C6GL00LF	D25P90C8GL00LF
37	69.32	63.50	55.68	55.30	49.68	D37P90C4GL00LF	D37P90C6GL00LF	D37P90C8GL00LF

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family D-SUB
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title MALE DELTA-D LOW PROFILE STRAIGHT PRESS-FIT
H	ELX-I-12654	AB	2015-10-26	angles	linear		
J	ELX-I-24020	AAB	2016-06-06	0°±2°	linear	scale 2:1	dwg no C01-8646-0369
				dr	PESSON	1995-10-03	
				engr	MITHUN PAUL	2016-06-06	type Product Customer Drawing
				chr	ATHUL A.B	2016-06-06	
				appd	BIJU K PAUL	2016-06-06	sheet 1 of 1 size A3
sheet index	revision	J					
	sheet	1					