Part Number : 783492044
Product Description : Impact 4 Pair, Right-Angle Power Header, 2 Modules with Right Hold-Down, Module 1: Blade P1 & P2 Length 6.90mm & Length 5.70mm; Module 2: Blade P1 & P2 Length 6.90mm, Blade B1 & B2 Length 5.70mm;Press-Fit, LCP, Glass Filled UL
Series Number : 78349
Status : Active
Product Category : Backplane Connectors



Documents and Resources

Drawings

783492044_sd.pdf

PK-78349-002-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

SYM-78349-2044-001.zip

Specifications

AS-76060-9997-001.pdf

PS-78213-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33; 34
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-

Downloaded from Arrow.com.

	DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	78349
Description	Impact 4 Pair, Right-Angle Power Header, 2 Modules with Right Hold-Down, Module 1: Blade P1 & P2 Length 6.90mm & Length 5.70mm; Module 2: Blade P1 & P2 Length 6.90mm, Blade B1 & B2 Length 5.70mm;Press-Fit, LCP, Glass Filled UL
Application	Conventional, Coplanar
Component Type	Power Header
Product Name	Impact
UPC	883906169817

Agency

UL	E29179

Downloaded from Arrow.com.

Electrical

Current - Maximum per Contact	20.0A
Data Rate	N/A
Shielded	No
Shield Type	N/A
Voltage - Maximum	250V

Physical

Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	Yes
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	20.675/g
Number of Columns	N/A
Number of Pairs	4
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.60mm
PC Tail Length	2.50mm
Pitch - Mating Interface	5.20mm
Pitch - Termination Interface	2.00mm, 3.20mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to PCB	No

Downloaded from Arrow.com.

Stackable	No
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Impact 4 Pair Vertical Power Receptacles	78214
Impact 4 Pair Right-Angle Power Receptacles	78350

Application Tooling

Downloaded from Arrow.com.