





1.Wiring Diagram.



P1 P2

2.Cable test condition :

Open / Short : 100%
Insulation resistance : 5M ohms
Contact resistance : 2 ohm
Hipot : DC 300V / 1 sec

3.Each pcs with PE polybag.

NO.	PART NO.	DESCRIPTION	QTY	UNIT/REF
5	CONN	USB3.0 A FEMALE G/F BLUE	1	P2
4	PVC	45P PVC BLACK OVERMOLD	25g	
3	PE	LLDPE 500026 6201	16g	
2	CONN	USB3.0 A/M G/F BLUE	1	P1
1	CABLE	《28AWG (7/0.12TC) *IP+D(7/0.10TC)+AL+M》*2+28AWG (7/0.12TC) *IP+24AWG(7/0.2TC)*2C+A+D+B (96/0.12AM) OD5.5 BLACK	1	3000mm
BILL OF MATERIAL				

A	INITIAL RELEASE	2014/08/28
REVECN#	DESCRIPTION	DATE
Cnc Tech,LLC	P/N: 103-1010-BL-00300	REV A
TITLE	CABLE USB3.0 A/M TO A/F	
DRAWN WENC	DATE 08/24/14	CUSTOMER P/N:
CHECKED EDWIN	08/24/14	CUSTOMER:
APPROVAL		SHEET 1 OF 1