




ELECTRICAL SPECIFICATIONS

FREQUENCY RANGE (GHz):	10.7 - 12.75
ISOLATION (dB):	23 MIN
INSERTION LOSS (dB):	0.30 MAX
VSWR:	1.20 MAX
POWER: AVG (PORT 1 TO 2):	10W
PEAK:	50W

MECHANICAL SPECIFICATIONS

CONNECTORS:	SMA-FEMALE, PASSIVATED STAINLESS STEEL
CONTACT PINS:	BERYLLIUM COPPER, GOLD PLATE
OPERATING TEMPERATURE:	-30° to +65°C
WEIGHT (APPROX):	0.74 OUNCES

DIMENSIONS IN INCHES, UNLESS OTHERWISE SPECIFIED		Dilom MICROWAVE INC. Fresno, California, USA	
TOLERANCE XX±0.03 XXX±0.010		TITLE 10.7 - 12.75 GHz SMA Circulator	
SCALE 6:1		MODEL NO D3C1012	REV