

SIGN	DATE	DESCRIPTION	APPROVER
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	

Material

- Insulator: Glass Filled Polyester
- Flammability: UL94V-0
- Contacts: Phosphor Bronze
- Contact Plating: See options
- Shell: Brass
- Shell Plating: 80u" Min. Tin over 50u" Cu

Ratings

- Current: 1A
- Voltage: 30V AC(r.m.s.)
- Contact Resistance: <30mU
- Insulation Resistance: >1,000 MU
- Dielectric Strength: 750V AC
- Operating Temp: -55° - +85°
- Storage Temp: -40° - +70°


RoHS Compliant

PART NUMBER:

USB-A1SSXX

COLOR: B: Black
W: White

PLATING: 6: Selective Gold Flash (Std.)
8: Selective 30u" Gold



Edge of PC Board

Recommended P.C. Board Layout

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

 ON-SHORE TECHNOLOGY, INC.							
TITLE	USB - A type, Side type, thru hole						
PART NO.	USB-A1SSXX			DWG NO.	USB-A1SSXX.DWG		
APPROVED	CHECKED	DESIGNED	DRAWN		4050		Tolerance
	Marvin 2006.11.12	Marvin 2006.11.12	Marvin 2006.11.12		UNIT: mm/inches		X* ±1°
					SCALE: NONE		X.X ±0.30/.012
				SHEET: 01/01		REV: A	X.XX ±0.20/.008
							X.XXX ±0.10/.004