



Home> Products > Wirewound Resistors > VP Adjustable > Product Page

Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

VP10FA500



Actual product appearance may vary.

VP Adjustable Series, 500 Ohms, 10.0 W, Adjustable, Wirewound Resistor

Features

- Adjustable slider
- Rugged vitreous enamel
- All-welded construction
- Meets or exceeds MIL-R-26 standards

Potential Applications

- Applications requiring adjustable resistance values
- Power supplies
- Power dissipation circuits
- Load adjustors for power amplifiers
- Voltage divider in DC circuits

Description

The VP Adjustable Series offer adjustable power resistors that are excellent for applications requiring settings at different resistance values. The resistors come equipped with an adjustable slider lug, making them ideal for adjusting circuits, obtaining odd resistance values and setting equipment to meet various line voltage requirements. The VP Adjustable series is made with tinned lug terminals solderable to MIL-R-26 standards. These resistors can be bracket mounted.

Note: Not suitable for high frequency applications.

Supporting Documentation

-  [Dimensions](#)
-  [Mounting Bracket](#)

Product Specifications	
Resistor Type	Adjustable
Power Rating	10 W
Resistance Value	500 Ohms
Terminal Type	Lug
Housing Material	Vitreous enamel
Tolerance	± 10%
Temperature Coefficient	± 100 ppm/ °C
Availability	Global
UNSPSC Code	32121608
UNSPSC Commodity	32121608 Wire Wound Resistor
Series Name	VP Adjustable

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

Specification Search