



**Part Number :** [1200878742](#)

**Product Description :** Nano-Change (M8) Double-Ended Cordset with Knurled Hexnut, 3 Poles, Female (Straight) to Male (90°), 24 AWG, WSOR Cable, 3.0m (9.84') Length

**Series Number :** 120087

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 443032B41M030



---

## Documents and Resources

### Drawings

[1200878742\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	120087
Description	Nano-Change (M8) Double-Ended Cordset with Knurled Hexnut, 3 Poles, Female (Straight) to Male (90°), 24 AWG, WSOR Cable, 3.0m (9.84') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Double Ended
UPC	889056074285

### Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V

### Physical

Cable Diameter	4.50mm (.177")
Cable Length	3.0m (9.84')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Nano-Change (M8)
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass

Material - Plating Mating	Gold
Orientation	90° to Straight
Poles	3
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	WSOR
Wire Size (AWG)	24

---

This document was generated on Dec 29, 2025