









Material	AISI 316L Stainless Steel (2,00 mm thick) front plate; AISI 316L Stainless steel (1,5 mm thick) buttons with built-in silicone rubber sealing gasket
Lettering	white opalescent polycarbonate infill
Button stroke	0,6 mm +/- 0,1 mm
Actuation force	4,0 N (typical)
Life expectancy	>3.000.000 cycles
IP Protection rate	IP65
Impact Protection Rate	IK08
Contact technology	Stainless steel metal dome on Gold plated PCB
Contact resistance	<30 Ohm (Vmax=12Vdc; Imax=20mA)
Insulation resistance	>500K Ohm (Vmax=12Vdc; Imax=20mA)
Operating temperature	-25°/+85°C
Storage temperature	-25°/+85°C

Pin-Out		
	Pin1	Pin2
Pin4	1	5
Pin5	3	7
Pin6	4	8
Pin7	2	6

Compliance: RohS III (2015/863/EU)

Tolerances: >0-6: ±0.05 mm >6-30: ±0.1 mm >30-120: ±0.15 mm			Date	Name	YME IP 12 H	
			04/12	dr		
Revised	06/21	dr			30 26 27	
IP rating	05/19	dr				
Rename	02/14	dr				
Rename	11/13	dr				
Modifications	Date	Name				

knitter-switch

30 26 27

Page

1/1