




FACE VIEW - FEMALE INSERT
SCALE 2 : 1




1 BROWN
3 BLUE
4 BLACK

1 BROWN
2 WHITE
3 BLUE
4 BLACK

1 BROWN
2 WHITE
3 BLUE
4 BLACK
5 GRAY



REF. KNOCK-OUT HOLE



REF. ATTACHED TO
BLUE WIRE

FINAL ASSEMBLY
1200700056 (SHOWN)

8	FLAG LABEL	VINYL	BLACK/YELLOW
7	PANEL NUT	STEEL	ZINC PLATED
6	WIRE, 22-1	PVC INSULATED	SEE FACE VIEWS
5	O-RING (MATING)	VITON	RED
4	O-RING (PANEL)	NITRILE	BLACK
3	CONTACT SOCKET	Cu ALLOY	GOLD PLATED
2	INSERT, FEMALE	NYLON	BLACK
1	SHELL	ALUMINUM	CLEAR ANODIZE
ITEM	DESCRIPTION	MATERIAL	FINISH

REDRAWN, ADD NOTES CORRECTED PIN-OUT CIRS 1 & 3 EC NO: JFG2017-0287 DRAWN BY: DRWNRSTONE CHKD BY: CHKDK COX APPR: TWOLDEGERIE/2016/09/16	REV	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 3:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION		
					mm	INCH	DRAWN BY NKUMAR01	DATE 27/08/09	TITLE MICRO-CHANGE RECEPTACLE M12 FEMALE, 22 AWG 1/4 NPT FRONT PANEL MT			
				4 PLACES	± ---	± ---	CHECKED BY BWOODMAN	DATE 27/08/09				
				3 PLACES	± ---	± ---	APPROVED BY JFMURPHY	DATE 2009/08/27				
				2 PLACES	± ---	± ---	MATERIAL NO. SEE P/N CHART				DOCUMENT NO. SD-120070-056	SHEET NO. 1 OF 1
				1 PLACE	± ---	± ---	ANGULAR ±1/2°		MOLEX MOLEX INCORPORATED			
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. ELECTRICAL SPECIFICATIONS
VOLTAGE RATING: 250V
CURRENT RATING: 4 AMPS
4. PROTECTION: IP67 (WHEN MATED)
5. DIMS SHOWN ARE FOR REFERENCE ONLY