Part Number: **RK163111OUZA** 16mm Size Metal Shaft Type RK163 Series

Document Edition: 4 Date: 2022/11/01

Basic Information | Dimensions | Mounting Hole Dimensions | Attached Parts | Packing Specifications | Soldering Conditions

Add to Favorites | Save Search | Contact

Basic Information

Active

Number of operating shafts	Single-shaft
Number of resistor elements	Single-unit
Control part orientation	Horizontal
Fixing method of bushing	Screw
Shaft type	Serrated
Terminal style	For PC board
Length of the shaft	15mm
Detent	Without
Total resistance	10kΩ
Resistance taper	LB
Dimensions	16mm Size

Specifications

Operating temperature range		-10°C to +70°C
Electrical performance	Total resistance tolerance	±20%
	Rated power	0.1W
	Maximum operating voltage	150V AC, 2V DC
	Residual resistance	200 max.
	Insulation resistance	100MΩ min. 500V DC
	Voltage proof	500V AC for 1 minute
Mechanical performance	Total rotational torque	30Ft·oz
	Rotational torque	3 to 15mN·m
	Stopper strength	1.5N·m
	Push-pull strength	100N max.
	Vibration	10 to 55 to 10Hz/min., the amplitude is 1.5mm or 98m/s² at the frequencies, in the 3 directions of X, Y and Z and for 2 hours each direction
Durability	Operating life	15,000 cycles
Minimum order unit(pcs.)	Japan	600
	Export	1,200

Dimensions

Open an interactive(3D) image in a separate window

Mounting Hole Dimensions

Open an interactive(3D) image in a separate window

Viewed from mounting side.

Attached Parts

Unit: mm

Open an interactive(3D) image in a separate window

These parts are attached to the following products.

Packing Specifications

Bulk

Number of packages (pcs.)	
1 case / pack	1
1 case / export packing	1,200

Export package measurements (mm)

532×320×386

Soldering Conditions

Reference for Hand Soldering

Tip temperature	
350°C max.	
Soldering time	
5s max.	
No. of solders	
1 time	

Notes are common to this series/models

1. This site catalog shows only such specifications. When using the products, please obtain formal specifications for supply.
2. Please advise purchase order when minimum order unit (integer).
3. Products other than those listed in above products are also available. Please contact us for details.

Cautions

Recommended Circuit Configuration

Please use the potentiometer in the voltage adjustment circuit (Fig. A). Avoid using it in the current adjustment circuit (Fig. B) as it is affected by the contact resistance between the resistive element and the wiper.

Direct Voltage

When direct voltage is flown through this part, terminal to terminal insulation may deteriorate depending on the use environment. This is due to a migration phenomenon. Contact us if you are planning to use this part under direct voltage.

Impedance on the Output Side

There is a possibility that might be affected by excessive resistance of resistive element and wiper in case of low impedance of output side in voltage regulation circuit. For this reason, we require that you adjust to impedance of output side more than 100 times of total resistance.

Residual Resistance

Although specific values of resistors are generally fixed for the product lineup, we provide certain custom-using the silver plates to enhance reliability against sulfurization. Contact us if you wish to use the part in a low-residual-resistance state.

Flow Contamination

Avoid exposing the potentiometer flow or water drops might occur on the surface of the resistor, etc. Deterioration of insulation or shorting may occur.

Soldering

To avoid potential contact issues, please do not solder wires to the top surface of the printed circuit board as shown in the diagram. Solder all metal tags into a substrate before use.

Stress Being Applied to the Terminals

Always pay special attention not to apply excessive stress when handling the terminals. Also, be sure to design appropriate soldering conditions.

Looseness of the Shaft

When lengthy shaft lengths are being employed, the looseness (deviation) tends to grow in proportion to the shaft length. Conducting a test under actual operating conditions is recommended.

Chassis Mounting

The use of a nut to fasten this part may lead to excessive tightening and can deteriorate the rotary contact performance, or strip the threads. Handle with care when tightening the nut.

Use of Chemicals

Since synthetic resins such as polyurethane are being used as the material for the insulated type shafts, avoid using this part under gross environments of such chemicals as ammonia, amines, alkali water solutions, aromatic hydrocarbons, ketones, esters and halogenated hydrocarbons, especially under their intensive gas environment.

Operation at Low Temperature

When these products are expected to be used under low-temperature environments such as applications for car radios and car stereos, we can customize them for easier and more smooth rotary movements. When giving orders, indicate whether the low-temperature specification is required. Thank you.

Storage

1. When the products are delivered, or after incorporation and humidity, without direct sunshine and corrosive gas ambient. Use them at an earliest possible time(1 year after the delivery).
2. After breaking the seal, keep the products in a plastic bag to shut out ambient air, store them in the same environment as above, and use them up as soon as possible.
3. Do not stock too many switches.

The above description is from the standard specification sheet of the "Precaution and Guideline of Potentiometer for Electrical Devices", which is a technical report issued by the Japan Electronics and Information Technology Industries Association (JEITA) in March 2002.
For details, see the above technical report.

Measurement and Test Methods

Electrical performance

Total Resistance

With the shaft (here) placed at the termination of terminal 1 or 3, total resistance shall be determined by measuring the resistance between the resistor terminals 1 and 2 unless otherwise specified. (Fig. 1)

Rated Power

Rated power shall be the maximum value of electric power that can be applied continuously to the whole area of a resistor between terminals 1 and 2 at the rated ambient temperature.
Derating curve shall be determined as follows: For a temperature exceeding the rated ambient temperature of 50 to 70°C shall be obtained by multiplying the rated power by the rated power ratio determined from the derating curve shown below.



Rated Voltage

Rated voltage is associated with the rated power and shall be determined by the following equation. When the resulting rated voltage exceeds the maximum operating voltage of a specific resistor, the maximum operating voltage shall be taken as the rated voltage.

$$E = \sqrt{P \times R}$$

E : rated voltage (V)
P : rated power (W)
R : total nominal resistance (Ω)

Top Resistance

Determined by measuring the resistance between a tap terminal and a specified terminal (terminal 1 or terminal 3).

Residual Resistance

With the shaft (here) placed at the termination of terminal 1, the residual resistance shall be measured between the terminals 1 and 2. Next, with the shaft placed at the end of terminal 3, the resistance shall be measured between the terminals 2 and 3. If there are tap terminals, the shaft (here) shall be turned around and the resulting minimum resistance between the tap terminal and the terminal 2 shall be measured.

Maximum Attenuation Level

With the shaft placed at the termination of terminal 1, maximum attenuation level shall be determined by measuring the voltage applied between the terminals 1 and 2 and that outputting the ratio to the voltage applied between the terminals 1 and 3.
Unless otherwise specified, the value obtained shall be used in place of the residual resistance of a rotary potentiometer for volume control.

Insertion Loss

With the shaft placed at the termination of terminal 3, insertion loss shall be determined as the measuring the voltage applied between the terminals 1 and 2 and that outputting the ratio to the voltage applied between the terminals 1 and 3.
Unless otherwise specified, the value obtained shall be used in place of the residual resistance of a rotary potentiometer for volume control.

Sliding Noise

Measured by connecting the resistor to an amplifier having frequency characteristics specified in JIS C 5401, applying DC voltage of 20V between the terminals 1 and 3 (if rated voltage is 20V or less, the voltage shall be applied) and by rotating (moving) the shaft (lever) at a speed of about 30 cycles per minute.

Voltage Withstand

Determined by applying AC voltage to the specified locations for one minute to checking for any arc, burning, dielectric breakdown and other abnormalities. Respective terminals may be tested together. The locations described below shall be tested unless otherwise specified. However, if the section concerned is so constructed as to conduct, that particular part shall not be tested.

Insulation Resistance

Determined by applying DC voltage to applying specified voltage to the specified locations.
The locations described below shall be tested unless specified. However, if the section concerned is so constructed as to conduct, that particular part shall not be tested.

Measuring Locations for Withstand Voltage and Insulation Resistance

- Between terminal and shaft (lever).
- Between terminal and metal cover (frame).
- Between terminals connected to separate resistor element and terminal connected to another resistor element (of multi-ganged unit).
- Between switch terminal and shaft.
- Between switch terminal and metal cover.
- Between switch terminal and metal cover

Gang Error

With the shaft (here) placed at the specified position, gang error shall be determined by applying test voltage of 2 to 10V (sine wave RMS value) between the terminals 1 and 3 (if rated voltage is 10V or less, the voltage between the terminal 1 and the specified terminal terminal 1 or 3) and then by using the following equation.
If there are no guidelines on determination, GE voltage may be applied for this test.

$$\text{Gang error} = \frac{V_2}{V_1} \times 200\text{g}$$

Where,
V1 : Voltage between the reference resistor terminals 1 and 2 voltage between the terminals 2 and 3 if the resistance tapers are C, Z and reverse (S)
V2 : Voltage between the non-reference resistor terminals 1 and 2 (voltage between the terminals 2 and 3 if the resistance tapers are C, Z and reverse (S))

If there is a tap terminal, measurement shall be made by connecting a fixed resistor whose resistance is equivalent to 1/10 of the nominal total resistance between the tap terminal and the terminal 1 (if the resistance taper is C, make connection between

Contact Resistance of Switch

Determined by measuring the contact resistance of switch shall be determined by measuring drop voltage when 5V DC, 1A is applied between contacts and the contacts are closed.

Mechanical Performance

Total Rotational Angle (Travel)

Determined by measuring the rotational angle (travel) when the shaft (lever) is turned (moved) from the termination position of terminal 1 to the termination position of terminal 3.

Rotational Torque (Operating Force)

Determined by measuring the torque (operating force) necessary to turn (move) the shaft (lever). Unless other specifications, measurement shall be made at an ambient temperature of 5 to 35°C, and the shaft rotational speed shall be 60° per second and the lever moving speed 20mm per second.

Starting Torque (Starting Force)

Determined by measuring a torque (operating force) necessary to turn (move) the shaft (lever) for the first time after allowing the test piece to stand for 1 hour or more at the ambient temperature of 5 to 35°C, and then, measurement shall be made at an ambient temperature of 5 to 35°C, and the shaft rotational speed shall be 60° per second and the lever moving speed 20mm per second.
Remarks:
1. To be specified only when required in particular.

Shaft Wobble

Determined by measuring the amount of deflection at a position of 30mm from the reference surface with a bending moment of 0.1N·m (10mN·m for insulated shaft) applied perpendicularly to the shaft from 180° different directions at a point within 5mm from the place where a bending moment of 0.1N·m (10mN·m for insulated shaft) is exerted. However, if the length of the shaft is less than 30mm, proportion calculation shall be used.

Allowable Operating Torque for Shaft (Lever)

With the shaft placed at the termination of terminal 1, a specified rotational moment (force) shall be applied at the direction for 10 seconds. Next, the shaft (lever) shall be placed at the termination of terminal 3 and a specified torsional moment (force) shall be applied similarly to check the current part and other sections for any deformation or breakage.

Push-pull Strength (Lever Push-pull Strength)

A specified force shall be applied to the axial direction of the shaft (lever) for 10 seconds to check the control part and other sections for any deformation or breakage and for operating condition.

Resistance Taper

Resistance Taper

With the shaft (here) placed in the specified position, resistance taper shall be determined by measuring the voltage between the specified terminals between terminals 1 and 2 or between terminals 2 and 3and calculating the percentage in reference to the voltage between terminals 1 and 3.
Reference: Standard resistance tapers in reference to rotational angles (travels) are as shown below.



Inquiries about Products

Category List

Sensors
Semiconductors
TACT Switch
Switches
Encoders
Potentiometers
Connectors
Wireless Communication Devices
Multi-Control Devices
Aspherical Glass Lenses
Actuators
haptic reactor
Capacitive Sensing Modules

ALPS ALPINE
© 2024 ALPS ALPINE CO., LTD.