

## AUTOMOTIVE CONNECTOR CAPS & COVERS



✓ Active

TE CONNECTIVITY (TE)

**PIN CONN CVR ASSY,8POS,AMPSEAL 16,90 DEG**

AMP | AMPSEAL 16

2302485-2

TE Internal Number: 2302485-2

EU RoHS Compliant

EU ELV Compliant

**Accessory Type** Backshell Kit

**Cable Exit Angle** 90

**Strain Relief** With

**Color** Black

**Material** PA

 **PRODUCT DRAWING**  
English

 **3D PDF**

## DOCUMENTATION

Product Drawings

**BACKSHELL AND ELBOW KIT, 8 POSN CAP ASSY, AMPSEAL 16**

PDF

English

CAD Files

**3D PDF**

PDF

**3D**

**Customer View Model**

2D\_DXF.ZIP

## English

### **Customer View Model**

3D\_IGS.ZIP

**English**

### **Customer View Model**

3D\_STP.ZIP

**English**

---

Product Specifications

Product Specification

### **108-151043**

PDF

**English**

---

Product Environmental Compliance

TE Material Declaration

### **MD\_2302485-2\_02172017939\_dmtec**

PDF

**English**

---

Instruction Sheets

Instruction Sheet (U.S.)

### **INSTRUCTION SHEET, AMPSEAL 16 BACKSHELLS, VERTICAL AND RIGHT ANGLE**

PDF

**English**

---

## **FEATURES**



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

Product Type Features

**Accessory Type** Backshell Kit

**Strain Relief** With

**Connector System** Wire-to-Wire

**Sealable** No

---

Configuration Features

**Number of Positions** 8

---

Body Features

**Cable Exit Angle** 90

**Color** Black

**Material** PA

---

Usage Conditions

**Operating Temperature Range** -40 – 125 °C [ -40 – 257 °F ]

---

Industry Standards

**UL Flammability Rating** UL 94V-0

---

Packaging Features

**Packaging Method** Bag/Box

---

Other

**Serviceable** Yes

Statement of Compliance

**Statement of Compliance**

PDF

---