



Micro Commercial Components



Micro Commercial Components
130 W Cochran St, Unit B
Simi Valley, CA 93065
Tel:818-701-4933

Features

- Halogen free available upon request by adding suffix "-HF"
- Internal Short Circuit Current Limiting
- Internal Thermal Overload Protection
- No External Components Required
- Maximum Output Current I_{CM} : 0.1A
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- Lead Free Finish/RoHS Compliant ("P" Suffix designates RoHS Compliant. See ordering information)

Maximum Ratings


Parameter	Symbol	Value	Unit
Input Voltage ($V_o=5.8V$)	V_1	30	V
Operating Junction Temperature	T_{OPR}	-40~+125	°C
Storage Temperature Range	T_{STG}	-55---+150	°C
Continuous Total Dissipation	P_D	0.625	W
Thermal Resistance From Junction to Ambient	$R_{\theta JA}$	160	°C/W

Electrical Characteristics ($V_i=10V$, $I_o=40mA$, $0^\circ C < T_j < 125^\circ C$, $C_1=0.33\mu F$, $C_o=0.1\mu F$, unless otherwise specified)

Parameter	Sym	Min	Typ	Max	Test conditions
Output Voltage	V_o	4.8V	5.0V	5.2V	$T_j=25^\circ C$
		4.7V		5.25V	$7V \leq V_1 \leq 20V$, $I_o=1mA-40mA$
		5.0V			
		4.7V		5.25V	$7V \leq V_1 \leq V_{MAX}$, $I_o=1mA-700mA$ (Note)
Load Regulation	ΔV_o		11mV	60mV	$I_o=1mA-100mA$, $T_j=25^\circ C$
			5.0mV	30mV	$I_o=1mA-40mA$, $T_j=25^\circ C$
Line regulation	ΔV_o		8mV	150mV	$7V \leq V_1 \leq 20V$, $T_j=25^\circ C$
			6mV	100mV	$8V \leq V_1 \leq 20V$, $T_j=25^\circ C$
Quiescent Current	I_q		2.0mA	5.5mA	$8V \leq V_1 \leq 20V$
			ΔI_q	1.5mA	
Quiescent Current Change	ΔI_q			0.1mA	$1mA \leq I_o \leq 40mA$
Output Noise Voltage	V_N		40 μV		$10Hz \leq f \leq 100KHz$
Ripple Rejection	RR	41dB	80dB		$8V \leq V_1 \leq 20V$, $f=120Hz$, $T_j=25^\circ C$
Dropout Voltage	V_d		1.7V		$T_j=25^\circ C$

*Note: Bypass Capacitors are recommended for optimum stability and transient response and should be located as close as possible to the regulators


Typical Application:



MC78L05BP

Three-Terminal Low Current Positive Voltage Regulator

TO-92



DIMENSIONS

DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	.175	.185	4.45	4.70	
B	.175	.185	4.45	4.70	
C	.500	---	12.70	---	
D	.016	.020	0.41	0.63	
E	.135	.145	3.43	3.68	
G	.095	.105	2.42	2.67	Straight Lead
	.173	.220	4.40	5.60	Bent Lead

* For ammo packing detailed specification, click here to visit our website of product packaging for details.

MC78L05BP

Figure 1. Representative Schematic Diagram





Figure 2. Power Derating Curve



Ordering Information :

Device	Packing
Part Number-AP	Ammo Packing: 20Kpcs/Carton
Part Number-BP	Bulk: 100Kpcs/Carton

Note : Adding "-HF" suffix for halogen free, eg. Part Number-AP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.