

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A11	REVISED PER ECO-21-001365	26JAN2021	DS	DS





SECTION A-A


1. SUGGESTED MOUNTING SCREW SIZE IS ∅2.50-3.00mm [∅0.099 - 0.118 INCH] SELF TAPPING THREAD FORMING SCREW, SUCH AS DELTA PT, TO BE DRIVEN AT 0.6-0.8 N-m THE CUSTOMER SHOULD TEST THE SCREW SIZE AND TYPE IN ORDER TO VERIFY THEIR SELECTION FOR THEIR APPLICATION

2. DATE CODE IN THIS LOCATION USING 5 DIGIT CODE FIRST 2 DIGITS = YEAR, SECOND 2 DIGITS = WEEK LAST DIGIT = DAY.

3. MATERIALS: HEADER HOUSING - GLASS FILLED PBT
PINS - TIN OR GOLD PLATED BRASS

4. HOUSING COLORS ARE MECHANICALLY KEYED TO MATE ONLY WITH IDENTICALLY COLORED PLUG ASSEMBLIES.

5. HEADER MATES TO PLUG ASSEMBLY 776273 WHICH USES REELED TERMINAL 770520 OR LOOSE PIECE TERMINAL 770854



776261-1 & 1-776261-1 SHOWN

HEADER COLOR 4	PLATING	PART NUMBER
BLUE	GOLD	1-776261-5
GRAY	GOLD	1-776261-4
NATURAL	GOLD	1-776261-2
BLACK	GOLD	1-776261-1
BLUE	TIN	776261-5
GRAY	TIN	776261-4
NATURAL	TIN	776261-2
BLACK	TIN	776261-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.2
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL 3

FINISH 3

DWN 04FEB2010 D. STRAUSSER
CHK 22MAR2010 D. STRAUSSER
APVD 27APR2010 D. STRAUSSER

PRODUCT SPEC 108-1329
APPLICATION SPEC 114-16016
WEIGHT 16.90g

TE Connectivity

NAME HEADER ASSEMBLY, 14 POSITION, VERTICAL, AMPSEAL

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-776261	-

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 2 | REV A11


4805 (3/13)

Downloaded from Arrow.com.


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




RECOMMENDED P.C. BOARD LAYOUT
FOR 1.57 THICK P.C. BOARD




RECOMMENDED MOUNTING HOLE LAYOUT
FOR 5.0 MAX THICK PANEL




SCALE 2:1



SECTION A-A
OPTIONAL CONSTRUCTION IF PANEL
THICKNESS IS GREATER THAN 2.0




SECTION A-A
OPTIONAL CONSTRUCTION IF PANEL
THICKNESS IS GREATER THAN 2.0




SCALE 2:1


ENSURE THE HEADER IS FLUSH
TO THE PANEL FACE ALL AROUND
BEFORE TIGHTENING TO FINAL TORQUE



776261-2 & 1-776261-2
KEY LOCATION
SCALE 2:1



776261-4 & 1-776261-4
KEY LOCATION
SCALE 2:1



776261-5 & 1-776261-5
KEY LOCATION
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.2
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL - -
FINISH - -

DWN 04FEB2010 D. STRAUSSER
CHK 22MAR2010 D. STRAUSSER
APVD 27APR2010 D. STRAUSSER
PRODUCT SPEC 108-1329
APPLICATION SPEC 114-16016
WEIGHT 16.90g

TE Connectivity

NAME HEADER ASSEMBLY, 14 POSITION, VERTICAL, AMPSEAL

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-776261	-

CUSTOMER DRAWING | SCALE 4:1 | SHEET 2 OF 2 | REV A11

4805 (3/13)

Downloaded from Arrow.com.